



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CF26DTEIN835 26W 4 Pin Triple Tube Biax GX24Q-3 3500K Compact *Sylvania-Ledvance*

Catalog Number	CF26DTEIN835
Manufacturer	Sylvania-Ledvance
Description	Dulux 26W Triple Compact Fluorescent Amalgam Lamp With 4 Pin Base, 3500K Color Temperature, 82 Cri, For Use With Electronic and Dimming Ballasts, Ecologic
Weight per unit	0.2300 (lbs/each)
Product Category	Integrated Non-Ballasted Lamps

### Features

amperage rating	Ballast Dependent
average life	16000
Base	GX24q-3
Lamp Type	DULUX T/E
lumens	1,746
Shape	T4
start type	ELECTRONIC RAPID START
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	26

### Material, Color, and Finish

color rendering index (cri)	82
color temperature	3500
Finish	Phosphor Coated

### Dimensions and Weight

Diameter	0.5000000000000000
Length	5

### Descriptions

Description	26W 4 PIN TRIPLE TUBE BIAx GX24Q-3 3500K COMPACT
extra long description	SYL CF26DT/E/IN/835/ECO/20881 CF26D
Long Description	DULUX 26W triple compact fluorescent amalgam lamp with 4 pin base, 3500K color temperature, 82 CRI, for use with electronic and dimming ballasts, ECOLOGIC
Product Type	CF26DTEIN835ECO 50/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135208812
Manufacturers Part Number	CF26DT/E/IN/835/ECO/20881
UPC	046135208812



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Compact Fluorescent

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Package	50
Weight Per each	0.23

## Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------