

# Specifications

## Eaton CHEC42N225L

Eaton CH surge loadcenter,Provisions only,Type CH surge ready loadcenter, Convertible,225 A,42 Circuits

### General specifications

<b>PRODUCT NAME</b>	Eaton CH surge loadcenter
<b>CATALOG NUMBER</b>	CHEC42N225L
<b>UPC</b>	782116200214
<b>PRODUCT LENGTH/DEPTH</b>	40 in
<b>PRODUCT HEIGHT</b>	4 in
<b>PRODUCT WIDTH</b>	15 in
<b>PRODUCT WEIGHT</b>	26 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	Order Cover CHSUR8LS or CHSUR8LF separately



*Powering Business Worldwide*

## Product specifications

<b>SPECIAL FEATURES</b>	Provisions only
<b>TYPE</b>	Surge loadcenter
<b>AMPERAGE RATING</b>	225 A
<b>BUS MATERIAL</b>	Aluminum
<b>NUMBER OF CIRCUITS</b>	42
<b>NUMBER OF SPACES</b>	42
<b>PHASE</b>	Single-phase
<b>ENCLOSURE</b>	NEMA 1
<b>INTERRUPT RATING</b>	25 kAIC

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
<b>MULTIMEDIA</b>	<a href="#">AFCI Educational Video</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHEC42N225L</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton CHEC42N225L

Eaton CH surge loadcenter,Provisions only,Type CH surge ready loadcenter, Convertible,225 A,42 Circuits

### General specifications

<b>PRODUCT NAME</b>	Eaton CH surge loadcenter
<b>CATALOG NUMBER</b>	CHEC42N225L
<b>UPC</b>	782116200214
<b>PRODUCT LENGTH/DEPTH</b>	40 in
<b>PRODUCT HEIGHT</b>	4 in
<b>PRODUCT WIDTH</b>	15 in
<b>PRODUCT WEIGHT</b>	26 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	Order Cover CHSUR8LS or CHSUR8LF separately

## Product specifications

<b>SPECIAL FEATURES</b>	Provisions only
<b>TYPE</b>	Surge loadcenter
<b>AMPERAGE RATING</b>	225 A
<b>BUS MATERIAL</b>	Aluminum
<b>NUMBER OF CIRCUITS</b>	42
<b>NUMBER OF SPACES</b>	42
<b>PHASE</b>	Single-phase
<b>ENCLOSURE</b>	NEMA 1
<b>INTERRUPT RATING</b>	25 kAIC

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
<b>MULTIMEDIA</b>	<a href="#">AFCI Educational Video</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHEC42N225L</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

