

# Specifications



Photo is representative

## Eaton CDR3044

Eaton Crouse-Hinds series PowerMate CDR receptacle, 30A, Four-wire, four-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series PowerMate CDR receptacle
<b>CATALOG NUMBER</b>	CDR3044
<b>UPC</b>	662276276963
<b>PRODUCT LENGTH/DEPTH</b>	2.88 in
<b>PRODUCT HEIGHT</b>	3.38 in
<b>PRODUCT WIDTH</b>	3.38 in
<b>PRODUCT WEIGHT</b>	2.2 lb



### Certifications and compliances

**AREA CLASSIFICATION** Ordinary/Non-Hazardous

### Product specifications

**AMPERAGE RATING** 30A

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	4X

<b>GROUNDING TYPE</b>	Style 1
<b>CONFIGURATION</b>	Four-wire, four-pole
<b>VOLTAGE RATING</b>	600 Vac/250 Vdc
<b>MATERIAL</b>	Copper-free aluminum

## Resources

**3D CAD DRAWING PACKAGE** [Eaton Crouse-Hinds CDR3044 3D drawing](#)

**BROCHURES** [PowerMate Drilling Pin and Sleeve Devices brochure](#)

**CATALOGS** [PowerMate Drilling Pin and Sleeve Devices catalog page](#)

**CERTIFICATION REPORTS** [PowerMate Drilling Pin and Sleeve Devices UL certification \(Receptacles\)](#)

**INSTALLATION INSTRUCTIONS** [IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - CDR3044](#)  
[PowerMate Connectors](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

---

Reserved.

