

# Eaton CHFAFGF115PN

Catalog Number: CHFAFGF115PN

Eaton CH arc fault / ground fault circuit breaker, Plug-on neutral, 15 A, 10 kAIC, Single-pole, CH

## General specifications



|   |                       |
|---|-----------------------|
| <b>Product Name</b>                               | <b>Catalog Number</b> |
| Eaton CH arc fault / ground fault circuit breaker | CHFAFGF115PN          |
|   | <b>UPC</b>            |
|   | 786670007838          |
| <b>Product Length/Depth</b>                       | <b>Product Height</b> |
| 3 in  | 0.75 in               |
| <b>Product Width</b>                              | <b>Product Weight</b> |
| 2 in  | 0.45 lb               |
| <b>Certifications</b>                             |                       |
| UL Listed   |                       |
| ANSI  |                       |

## Product specifications

### Type

Arc Fault / Ground Fault Circuit Breakers

### Special features

Plug-on neutral

### Amperage Rating

15 A

### Circuit breaker type

CH

### Interrupt rating

10 kAIC

### Number of poles

Single-pole

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHFAFGF115PN](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton CHFAFGF115PN

Catalog Number: CHFAFGF115PN

Eaton CH arc fault / ground fault circuit breaker, Plug-on neutral, 15 A, 10 kAIC, Single-pole, CH

## General specifications



|   |                |
|---|----------------|
| Product Name                                      | Catalog Number |
| Eaton CH arc fault / ground fault circuit breaker | CHFAFGF115PN   |

UPC  
786670007838

|                      |                |
|----------------------|----------------|
| Product Length/Depth | Product Height |
| 3 in                 | 0.75 in        |

|               |                |
|---------------|----------------|
| Product Width | Product Weight |
| 2 in          | 0.45 lb        |

### Certifications

UL Listed  
ANSI

## Product specifications

### Type

Arc Fault / Ground Fault Circuit Breakers

### Special features

Plug-on neutral

### Amperage Rating

15 A

### Circuit breaker type

CH

### Interrupt rating

10 kAIC

### Number of poles

Single-pole

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHFAFGF115PN](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)