



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CGB5915 1-1/2" Dia Male Cord Grip (1.625-1.875)

Crouse-Hinds

Catalog Number	CGB5915
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series CGB Cable Gland, Cable Range Min/Max: 1.625-1.875", Non-Armoured and Tray Cable, Non-Armoured, Steel, General Purpose, 1-1/2" NPT
Weight per unit	2.7 (lbs/each)
Product Category	Cable & Cord Grips

Features

connection	Male NPT
dimensions	3.4400 IN X 3.0000 IN X 3.0000 IN
Material	Aluminum Body and Gland Nut, Neoprene Seal

Dimensions and Weight

Size	1-1/2 in
------	----------

Descriptions

Description	1-1/2" DIA MALE CORD GRIP (1.625-1.875)
extra long description	CRS-H CGB5915 1 1/2 NPT MALE CORD/C
Features	They are also listed for use with tray cable types TC, TC-ER, TC-ER-HLA, ITC, ITC-ER, ITC-HL, PLTC and PLTC-ER. When installed in accordance with NEC501.10(B)(4), CGB, CGD, CGE and CGFP non-armoured glands are suitable for use in Class I, Division 2 hazardous locations. Crouse-Hinds series CGB, CGD, CGE and CGFP non-armoured glands are installed to provide a means for passing a cord, unarmoured cable or flexible conduit into an enclosure. The glands form an environmental seal for cord or unarmoured round
Long Description	Eaton Crouse-Hinds series CGB cable gland, Cable range min/max: 1.625-1.875", Non-armoured and tray cable, Non-armoured, Steel, General purpose, 1-1/2" NPT
Product Type	1 1/2 NPT Male Cord/Cab FTG Neo Bush
Special Features	Non-Armored Gland, Cord Size 1.000 To 1.188 In

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274139609
Manufacturers Part Number	CGB5915
UPC	782274139609

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	2.68

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 2
standard	UL (CANADA AND US)
Temperature Rating	-25 To 40 Deg C