



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHQ215 Type CHQ Classified BRKR 15A/2 Pole 120/240V 10K

Eaton Corp

Catalog Number	CHQ215
Manufacturer	Eaton Corp
Description	3/4" Thermal Magnetic Circuit Breakers, Type CHQ 3/4-Inch Classified Replacement Breaker, 15 A, 10 Kaic, Two-Pole, 120/240V, CHQ, Common Breaker Trip, (1) #14-8 Awg, (2) #14-10 Awg Cu/Al, CHQ, Type CH Loadcenters
Weight per unit	0.6000 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Features

amps	15
dimensions	2.5000 IN X 1.5000 IN X 3.0000 IN
interrupt rating	10
pole	Double
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	TYPE CHQ CLASSIFIED BRKR 15A/2 POLE 120/240V 10K
extra long description	ETN CHQ215 CHQ Classified 15A/2 Pol
Features	Eaton UL classified replacement circuit breakers are available in both 3/4-inch Type CHQ and 1-inch Type CL, single- and two-pole configurations. These breakers are classified as direct replacements by Underwriters Laboratories. In addition to a UL listing, they also come with a 15-year warranty.
Long Description	3/4" Thermal magnetic circuit breakers, Type CHQ 3/4-Inch classified replacement breaker, 15 A, 10 kAIC, Two-pole, 120/240V, CHQ, Common breaker trip, (1) #14-8 AWG, (2) #14-10 AWG Cu/Al, CHQ, Type CH Loadcenters
Product Type	CHQ Classified 15A/2 Pole 120/240V 10K

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113010892
Manufacturers Part Number	CHQ215
UPC	782113010892

Taxonomies, Classifications, and Categories

Category Description	CLASSIFIED BREAKERS
Type	3/4" Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.6

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative Energy Marine Vessels and Equipment - Marine Vessels and Equipment - Other Generation - Conventional Energy - Conventional Energy Datacenters - IT Space: CI and Hyper Converged Other
standard	UL 489