



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH24L225R 1PH/CH Loadcenter 225A Mlo 24 Cir. Cu Bus Nema 3R *Eaton Corp*

Catalog Number	CH24L225R
Manufacturer	Eaton Corp
Description	Eaton CH Main Lug Loadcenters, Standard, Main Lug Only, 225A, D, Copper, Nema 3R, Metallic, Overhead, CH, 24, 24, Three-Wire, Single-Phase, 120/240 V, #4 Awg-300 Kcmil
Weight per unit	29.0 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

Features

amperage rating	225
number of spaces	24
Phase	1
Voltage Rating	120/240 V

Dimensions and Weight

Depth	21
Height	5.19
Size	D
Width	14.31

Descriptions

Description	1PH/CH LOADCENTER 225A MLO 24 CIR. CU BUS NEMA 3R
extra long description	ETN CH24L225R Eaton CH main lug loa
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main lug loadcenters,Standard,Main lug only,225A,D,Copper,NEMA 3R,Metallic,Overhead,CH,24,24,Three-wire,Single-phase,120/240 V,#4 AWG-300 kcmil
Product Type	Eaton CH Main Lug Loadcenter
Special Features	Standard



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113097749
Manufacturers Part Number	CH24L225R
UPC	782113097749

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main lug loadcenter

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	29

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
standard	UL 67,UL 50