



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH24L3125R 3PH/CH Loadctr 125A Mlo 24 Cir. Cu Bus Nema 3R *Eaton Corp*

Catalog Number	CH24L3125R
Manufacturer	Eaton Corp
Description	Eaton CH Main Lug Loadcenter, Standard, Main Lug Only, 125 A, C, Copper, Nema 3R, Metallic, Overhead, CH, 24 Circuits, 24 Spaces, Four-Wire, Three-Phase, #1-4/0 Awg
Weight per unit	25.0 (lbs/each)
Product Category	Three Phase Main Lug Load Cent

Features

amperage rating	125
interrupt rating	35
media	Yes
number of spaces	24
Phase	3

Dimensions and Weight

Depth	29.13
Height	5.19
Size	C
Width	14.31

Descriptions

Description	3PH/CH LOADCNTR 125A MLO 24 CIR. CU BUS NEMA 3R
extra long description	ETN CH24L3125R 3Ph/CH LC 125A MLO 2
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main lug loadcenter, Standard, Main lug only, 125 A, C, Copper, NEMA 3R, Metallic, Overhead, CH, 24 Circuits, 24 Spaces, Four-wire, Three-phase, #1-4/0 AWG
Product Type	3PH/CH LC 125A Mlo 24 CKT Cu Bus N3R
Special Features	Standard



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113097664
Manufacturers Part Number	CH24L3125R
UPC	782113097664

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main lug loadcenter

Packaging

Carton	1
Weight Per each	25

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL 50,UL 67