



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHB120 CHB Bolt-In Sftybrkr Aic

Eaton Corp

Catalog Number	CHB120
Manufacturer	Eaton Corp
Description	Eaton CH Thermal Magnetic Circuit Breaker, Ground Fault Circuit Breaker, 5 Ma Ground Fault, 20 A, 10 Kaic, Single-Pole, 120/240 V, #14-8 Awg, CHB, CH Loadcenters
Weight per unit	0.2800 (lbs/each)
Product Category	1 Pole Standard Trip Bolt-On

Features

dimensions	8.3000 IN X 4.5000 IN X 4.4000 IN
interrupt rating	10 kAIC
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	CHB BOLT-IN SFTYBRKR AIC
extra long description	ETN CHB120 CHB BOLT-IN SFTYBRKR AIC
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneously.
Long Description	Eaton CH thermal magnetic circuit breaker, Ground fault circuit breaker, 5 mA Ground fault, 20 A, 10 kAIC, Single-pole, 120/240 V, #14-8 AWG, CHB, CH Loadcenters
Product Type	CHB Bolt-In Sftybrkr Aic
Special Features	5 mA Ground fault

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113112350
Manufacturers Part Number	CHB120
UPC	782113112350

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.28

Uses, Certifications, and Standards

Application	OtherDatacenters - IT Space: CI and Hyper ConvergedGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyMarine Vessels and Equipment - Marine Vessels and Equipment - OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL 489, Contact Manufacturer