

Eaton CHFCAF120PN

Catalog Number: CHFCAF120PN

Eaton CH AFCI circuit breaker, AFCI Branch feeder circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240 V, CH, Pigtail, Type CH Loadcenters, Plug-on neutral



Photo is representative

General specifications

| | |
|-------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton CH AFCI circuit breaker | CHFCAF120PN |
| UPC | Product Length/Depth |
| 786685546209 | 3.5 in |
| Product Height | Product Width |
| 3 in | 1 in |
| Product Weight | Warranty |
| 0.5 lb | Limited lifetime |
| Compliances | Certifications |
| HACR Rated | UL Listed |

Catalog Notes

Switching Duty Rated, HACR Rated

Product specifications

Used with

Type CH Loadcenters

Type

AFCI Branch feeder circuit breaker

Amperage Rating

20 A

Voltage rating

120/240 V

Neutral

Plug-on neutral

Interrupt rating

10 kAIC

Main circuit breaker

CH

Connection

Pigtail

Number of poles

Single-pole

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHFCAF120PN](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CHFCAF120PN

Catalog Number: CHFCAF120PN

Eaton CH AFCI circuit breaker, AFCI Branch feeder circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240 V, CH, Pigtail, Type CH Loadcenters, Plug-on neutral



Photo is representative

General specifications

| | |
|-------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton CH AFCI circuit breaker | CHFCAF120PN |
| UPC | Product Length/Depth |
| 786685546209 | 3.5 in |
| Product Height | Product Width |
| 3 in | 1 in |
| Product Weight | Warranty |
| 0.5 lb | Limited lifetime |
| Compliances | Certifications |
| HACR Rated | UL Listed |

Catalog Notes

Switching Duty Rated, HACR Rated

Product specifications

Used with

Type CH Loadcenters

Type

AFCI Branch feeder circuit breaker

Amperage Rating

20 A

Voltage rating

120/240 V

Neutral

Plug-on neutral

Interrupt rating

10 kAIC

Main circuit breaker

CH

Connection

Pigtail

Number of poles

Single-pole

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHFCAF120PN](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)