

# Specifications



Photo is representative



## Eaton CHFGF115

Eaton CH GFCI circuit breaker, Ground fault circuit breaker, Trip flag, GFCI, 15 A, 10 kAIC, Single-pole, 120/240 V, CHFGF, Ground fault circuit interrupter, GFI

### General specifications

<b>PRODUCT NAME</b>	Eaton CH GFCI circuit breaker
<b>CATALOG NUMBER</b>	CHFGF115
<b>UPC</b>	786685546216
<b>PRODUCT LENGTH/DEPTH</b>	3.5 in
<b>PRODUCT HEIGHT</b>	1.5 in
<b>PRODUCT WIDTH</b>	6 in
<b>PRODUCT WEIGHT</b>	1 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL 489
<b>CATALOG NOTES</b>	Switching Duty Rated, HACR Rated



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Ground fault circuit breaker
<b>SPECIAL FEATURES</b>	Trip flag, GFCI
<b>AMPERAGE RATING</b>	15 A
<b>VOLTAGE RATING</b>	120/240 V
<b>CIRCUIT PROTECTION</b>	Ground fault circuit interrupter
<b>INDICATORS</b>	GFI
<b>INTERRUPT RATING</b>	10 kAIC
<b>MAIN CIRCUIT BREAKER</b>	CHFGF
<b>NUMBER OF POLES</b>	Single-pole

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHFGF115</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton CHFGF115

Eaton CH GFCI circuit breaker, Ground fault circuit breaker, Trip flag, GFCI, 15 A, 10 kAIC, Single-pole, 120/240 V, CHFGF, Ground fault circuit interrupter, GFI

### General specifications

<b>PRODUCT NAME</b>	Eaton CH GFCI circuit breaker
<b>CATALOG NUMBER</b>	CHFGF115
<b>UPC</b>	786685546216
<b>PRODUCT LENGTH/DEPTH</b>	3.5 in
<b>PRODUCT HEIGHT</b>	1.5 in
<b>PRODUCT WIDTH</b>	6 in
<b>PRODUCT WEIGHT</b>	1 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL 489
<b>CATALOG NOTES</b>	Switching Duty Rated, HACR Rated



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Ground fault circuit breaker
<b>SPECIAL FEATURES</b>	Trip flag, GFCI
<b>AMPERAGE RATING</b>	15 A
<b>VOLTAGE RATING</b>	120/240 V
<b>CIRCUIT PROTECTION</b>	Ground fault circuit interrupter
<b>INDICATORS</b>	GFI
<b>INTERRUPT RATING</b>	10 kAIC
<b>MAIN CIRCUIT BREAKER</b>	CHFGF
<b>NUMBER OF POLES</b>	Single-pole

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHFGF115</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

