



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1701 North Jackson Suite E
78501-0000, TX McAllen
Phone: 956-331-2410
Fax: 956-331-2411



CHP24B150R CH Pon Loadctr 150A Main BRKR 24 Space N3R

Eaton Corp

Catalog Number	CHP24B150R
Manufacturer	Eaton Corp
Description	Eaton CH Main Breaker Loadcenters, Cover Included, Main Breaker, 150 A, X5, Copper, Nema 3R, Metallic, CSR, 48, 24, Three-Wire, Single-Phase, Overhead, 120/240 V
Weight per unit	27.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	150
media	Yes
number of spaces	24
Phase	1
Voltage Rating	120/240 V

Dimensions and Weight

Depth	29
Height	5.19
Size	X5
Width	14.31

Descriptions

Description	CH PON LOADCNTR 150A MAIN BRKR 24 SPACE N3R
extra long description	ETN CHP24B150R CH PON LC, 150A, MB,
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main breaker loadcenters,Cover included,Main breaker,150 A,X5,Copper,NEMA 3R,Metallic,CSR,48,24,Three-wire,Single-phase,Overhead,120/240 V
Product Type	CH Pon LC, 150A, MB, 24SP, N3R
Special Features	Cover included



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1701 North Jackson Suite E
78501-0000, TX McAllen
Phone: 956-331-2410
Fax: 956-331-2411

Manufacturer Information

Brand	Eaton
GTIN	00786689058593
Manufacturers Part Number	CHP24B150R
UPC	786689058593

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main breaker loadcenter

Packaging

Carton	1
Weight Per each	27

Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL 50,UL 67