



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CL710 600A Ac/DC Auto-Ranging Digital Pro Clamp Meter

*Klein Tools*

Catalog Number	CL710
Manufacturer	Klein Tools
Description	Klein Tools CL710 Clamp Meter Delivers Accurate Measurements Across Ac/DC Current, Voltage, Resistance, Continuity, Frequency, and Capacitance, All With True RMS Precision. It Features Diode Testing and A Low Impedance (Loz) Mode to Eliminate Ghost Voltages. The Clamp Features NCV Detection With Escalating Audio-Visual Alerts The Closer to The Voltage Source. The Transflective Reverse-Contrast Display and Lighted Dial Ensure Visibility In Any Lighting A Reliable Tool For Diverse Applications.
Weight per unit	0.7370 (lbs/each)
Product Category	Tools & Testers

### Features

ac voltage	1000V
Accuracy	See Instructions
auto ranging	Yes
auto-power off	Yes
Capacitance	6000 $\mu$ F
display	Transflective Reverse-Contrast with 6000 Count LCD
functions	AC/DC Voltage, AC/DC Current, Resistance, Audible Continuity, Low Impedance, Non-Contact Voltage Testing, Diode Test, Capacitance, Frequency/Duty Cycle, Min/Max Value, Rel/Zero, Data Hold Capability
included	Clamp Meter; Right-Angle Input Test Leads; Storage Pouch; Instruction Manual; and 3 x AAA Batteries
Material	ABS/Electronics
Overall Height	1.65" (4.2 cm)
Overall Width	3.47" (8.8 cm)
Temperature Range	-
Voltage	1000V AC; 1000V DC

### Dimensions and Weight

Overall Length	9.06" (2.30 cm)
----------------	-----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	600A AC/DC AUTO-RANGING DIGITAL PRO CLAMP METER
extra long description	KLEIN CL710 600A AC/DC Digital Pro
Long Description	Klein Tools CL710 Clamp Meter delivers accurate measurements across AC/DC current, voltage, resistance, continuity, frequency, and capacitance, all with True RMS precision. It features diode testing and a Low Impedance (LoZ) mode to eliminate ghost voltages. The clamp features NCV detection with escalating audio-visual alerts the closer to the voltage source. The transfective reverse-contrast display and lighted dial ensure visibility in any lighting a reliable tool for diverse applications.
Product Type	600A Ac/DC Digital Pro Clamp Meter
Special Features	Transflective Reverse-Contract Display; Lighted Dial; Built-in Lead Holder

## Manufacturer Information

Brand	Klein Tools
GTIN	00092644694493
Manufacturers Part Number	CL710
UPC	092644694493

## Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
Type	Pro Clamp Meter

## Packaging

Carton	1
Package	6
Weight	13 oz (369 g) Including Batteries
Weight Per each	0.737

## Uses, Certifications, and Standards

Application	Variety of electrical diagnostic and troubleshooting applications
standard	CAT IV 600V, CAT III 1000V, Class 2, Double Insulation, CE, UKCA