




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4406 Highway 28 East
71360-0000, LA Pineville
Phone: 318-767-0900
Fax: 318-767-0010



CLT50FC20 Loom Tubing *Panduit Corporation*

Catalog Number	CLT50FC20
Manufacturer	Panduit Corporation
Description	The CLT50F-C20 Polyethylene Corrugated Loom Tubing Protects Cables From Impact and Abrasion. Features A Slit For Easy Installation Onto A Bundle Of Wires or A Pre-Assembled Harness Assembly, Increasing Productivity. Hold In Place With Cable Ties and Accessories. Suitable For Indoor Applications. UL94-HB Flammability Rating and A Maximum Temperature Rating Of 122°F (50°C). Polyethylene. Inside Diameter 0.518" (13.16MM). Color Black. 1 Per Package.
Weight per unit	4.0 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Inside Diameter	0.52
Material	Polyethylene
media	Yes
outside diameter	0.67

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Length	100
--------	-----

Descriptions

Description	LOOM TUBING
extra long description	PAN CLT50F-C20 Corr. Loom Tubing Sl
Long Description	The CLT50F-C20 Polyethylene Corrugated Loom Tubing protects cables from impact and abrasion. Features a slit for easy installation onto a bundle of wires or a pre-assembled harness assembly, increasing productivity. Hold in place with cable ties and accessories. Suitable for indoor applications. UL94-HB flammability rating and a maximum temperature rating of 122°F (50°C). Polyethylene. Inside diameter 0.518" (13.16mm). Color Black. 1 per package.
Product Type	Corr. Loom Tubing Slit, .5" (12.7MM) X 100', Black, PK1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4406 Highway 28 East
71360-0000, LA Pineville
Phone: 318-767-0900
Fax: 318-767-0010

Manufacturer Information

Brand	PANDUIT
GTIN	00074983287123
Manufacturers Part Number	CLT50F-C20
UPC	074983287123

Taxonomies, Classifications, and Categories

Category Description	HEAT/COLD SHRINK
Type	Corrugated Loom Tubing

Packaging

Carton	10
Package	4
Weight Per each	4

Uses, Certifications, and Standards

Application	Covers wire and cable to protect from abrasion
standard	RoHS Compliant
Temperature Rating	122