



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS320I 20A 120/277VAC S Wire Comm 3W SW Iv

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | CS320I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Commercial 3-Way Switch, Side-Wire, 20A 120/277V. These Switches Offer Excellent Value While Meeting Federal Specification Standards. External Screw-Pressure-Plate Back Wiring Enables Fast Installation and Superior Electrical Connections. Rugged Construction Shrugs Off Hard Use and Abuse. |
| Weight per unit | 0.1500 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------------|--|
| action | Three pole |
| amperage rating | 20 |
| connection | Side Wire or external screw-pressure plate |
| Connection Type | Wired |
| Contact Configuration | One piece brass alloy contact arm |
| Contact Rating | Oversized silver alloy contacts |
| Degree of Protection | 1500V Dielectric Withstand Voltage |
| indoor/outdoor | Indoor |
| insulation | False |
| Material | Thermoplastic |
| media | Yes |
| Poles | 3-way |
| Switch Type | Toggle |
| Voltage | 120/277 V |
| Voltage Rating | 120/277 |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| extra long description | P&S CS20AC3I 20A 120/277VAC S WIRE |
| Long Description | Commercial 3-Way Switch, Side-Wire, 20A 120/277V. These switches offer excellent value while meeting federal specification standards. External screw-pressure-plate back wiring enables fast installation and superior electrical connections. Rugged construction shrugs off hard use and abuse. |
| Product Type | 20A 120/277VAC S Wire Comm 3W SW I |
| Special Features | Side wire, locking support, heavy duty toggle |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007126532 |
| Manufacturers Part Number | CS20AC3I |
| UPC | 785007126532 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Commercial switches |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.15 |

Uses, Certifications, and Standards

| | |
|-----------------------|--|
| Application | Commercial |
| Enclosure | Nylon |
| Mounting | WALL |
| nema rating | WD-1 and WD-6 |
| Operating Temperature | -40°-115°F |
| standard | CULUS, UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2, FEDSPEC |