



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **CS6364C LKG Conn, 50A 125/250V, 3P4W** *Hubbell Wiring Devices*

|                  |   |
|------------------|---|
| Catalog Number   | CS6364C   |
| Manufacturer     | Hubbell Wiring Devices  |
| Description      | Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-Nema, Screw Terminal, Black and White |
| Weight per unit  | 1.2 (lbs/each)  |
| Product Category | Plugs, Connectors, Inlets, Out  |

### **Features**

|                      |                         |
|----------------------|-------------------------|
| amperage rating      | 50                      |
| connection           | Pressure Screw Terminal |
| Current Rating       | 50                      |
| insulation           | Insulated Body          |
| Material             | Nylon                   |
| Number of Conductors | 4                       |
| pallet quantity      | 1190                    |
| Poles                | 3-Pole                  |
| Voltage Rating       | 125/250                 |

### **Material, Color, and Finish**

|       |             |
|-------|-------------|
| Color | Black;White |
|-------|-------------|

### **Dimensions and Weight**

|      |                             |
|------|-----------------------------|
| Size | 6.50 in x 2.56 in x 2.50 in |
|------|-----------------------------|

### **Descriptions**

|                        |   |
|------------------------|---|
| Description            | LKG CONN, 50A 125/250V, 3P4W  |
| extra long description | HWDK CS6364C LKG CONN, 50A 125/250V   |
| Features               | Hubbell's 50 Amp Twist-Lock® Devices feature a heavy-duty design and super-tough nylon housing built for heavy-duty applications and impact resistance, even in the harshest environments. Their rigid construction restricts contact distortion, minimizing the possibility of mating dissimilar devices. The cord grip's offset gripping jaws securely hold the conductors and the cord jacket for excellent strain relief. |
| Long Description       | Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black and White   |
| Product Type           | LKG Conn, 50A 125/250V, 3P4W  |
| Special Features       | Standard Product  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                       |
|---------------------------|-----------------------|
| Brand                     | WIRING DEVICE-KELLEMS |
| GTIN                      | 00783585827971        |
| Manufacturers Part Number | CS6364C               |
| UPC                       | 783585827971          |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES |
| Type                 | Connector Body                                      |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 10   |
| Weight Per each | 1.15 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Heavy Duty Industrial                           |
| environmental conditions | Indoor Dry unless protected by additional means |
| Mounting                 | Cord  |
| nema rating              | Non-NEMA  |
| standard                 | Certified to CSA C22.2 No.42;Listed to UL 498   |