



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CPS152R 2W-3P RCPT *Crouse-Hinds*

Catalog Number	CPS152R
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Arktite CPS Receptacle, 20A, Two-Wire, Three-Pole, Brass Contacts, 60 HZ, Style 2, 1 HP, Copper-Free Aluminum, Factory Sealed, Delayed Action Circuit Breaking, 125-250 Vac/18 VDC
Weight per unit	2.0 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

dimensions	5.1300 IN X 5.0000 IN X 5.8800 IN
Voltage Rating	125 To 250 Vac at 60 Hz, 18 Vdc

Dimensions and Weight

Height	6-23/32
Width	8

Descriptions

Description	2W-3P RCPT
extra long description	CRS-H CPS152R 20A 2W3P FS DELAY RCP
Features	Arktite CPS receptacles and CPP plugs from Eaton Crouse-Hinds Division are used with portable electrically operated devices such as motor generator sets, compressors, conveyors, portable tools and lighting systems. Used in locations that are hazardous due to the presence of flammable vapors or gases, and in damp or corrosive locations. Applicable for petroleum refineries, chemical and petrochemical plants and other process industry facilities.
Long Description	Eaton Crouse-Hinds series Arktite CPS receptacle, 20A, Two-wire, three-pole, Brass contacts, 60 Hz, Style 2, 1 HP, Copper-free aluminum, Factory sealed, Delayed action circuit breaking, 125-250 Vac/18 Vdc
Product Type	20A 2W3P FS Delay RCPT
Special Features	Power Rating 1 Hp at 125 To 250 Vac

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274182209
Manufacturers Part Number	CPS152R
UPC	782274182209



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Pin & Sleeve Devices

Type RECEPTACLE

Packaging

Carton 1

Weight Per each 2

Uses, Certifications, and Standards

Application Ind Facilities & Factories - Facility: Power Distribution and Control

standard UL 1010, CSA C22.2