



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS320I Switch, Spec, 3W, 20A 120/277V, Iv *Hubbell Wiring Devices*

| | |
|------------------|---|
| Catalog Number | CS320I |
| Manufacturer | Hubbell Wiring Devices |
| Description | Toggle Switch, 1 Pole, 3 Ways, 20 A, 120 to 277 V Ac, SPDT Contact Configuration, Thermoset (Body);Nylon (Toggle) Material, Steel Contact Material, Ivory, Back and Side Wired Connection, Screw Mount, Zinc Plated (Bridge), 1.49 In (L) X 1 In (W) X 4.18 In (H), -40 °C Operating Temperature, +75 °C Operating Temperature, 0.15 LB |
| Weight per unit | 0.0730 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|------------------|-----------------|
| action | SPDT |
| amperage rating | 20 |
| connection | Side Wired Only |
| Contact Rating | Per UL 20 |
| insulation | False |
| operating cycles | 50,000 |
| pallet quantity | 5000 |
| Poles | Single Pole |
| Switch Type | Toggle |
| Wattage | 5540 |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | 4.18 in x 1.49 in x 1.83 in |
|------|-----------------------------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | SWITCH, SPEC, 3W, 20A 120/277V, IV |
| extra long description | HWDK CS320I SWITCH, SPEC, 3W, 20A 1 |

Manufacturer Information

| | |
|--------|-----------------------|
| Brand | WIRING DEVICE-KELLEMS |
| GTIN | 00783585902159 |
| series | General Purpose |
| UPC | 783585902159 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Commercial switches |
| Type | TOGGLE |

Packaging

| | |
|-----------------|-------|
| Carton | 10 |
| Weight Per each | 0.073 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Enclosure | None |
| environmental conditions | Indoor Dry unless protected by additional means |
| Mounting | Screw Mount |
| standard | UL Listed |