



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

CSVTL48AL03MVOLT 4' Lumen and CCT Selectable Led Vaportight

Lithonia Lighting - Acuity

Catalog Number	CSVTL48AL03MVOLT
Manufacturer	Lithonia Lighting - Acuity
Description	The CSVT™ Vapor Tight Led Strip Light By Lithonia Lighting Is Built On The Technological Framework Of The CSS and Uses A Tongue & Groove, Poured In Gasket Design, Allowing For Easy, On The Go Maintenanceand Provides For Impressive Ratings Such As Csa Wet Location, IP65, IP66 For General Washdown, and NEMA4X!
Weight per unit	5.2 (lbs/each)
Product Category	Lighting

Features

average life	60
dimensions	50.3 x 5.4 x 3.8
Fixture Type	Low Bay
Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
lumens	3000 ,4000 ,5000 ,Switchable
Material	Polycarbonate
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Warranty	5
Wattage	47.6

Material, Color, and Finish

Color	Gray
Lens Color	WHITE
Lens Material	Polycarbonate
Style	Traditional

Dimensions and Weight

Height	3.8
Length	50.3
Width	5.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	New Construction,Remodel
Description	4' LUMEN AND CCT SELECTABLE LED VAPORTIGHT
extra long description	LITH CSVT L48 ALO3 MVOLT SWW3 80CRI
Features	Contractor Select
Long Description	The CSVT™ Vapor Tight LED Strip Light by Lithonia Lighting is built on the technological framework of the CSS and uses a tongue & groove, poured in gasket design, allowing for easy, on the go maintenanceand provides for impressive ratings such as CSA wet location,IP65, IP66 for general washdown, and NEMA4X!
Product Type	Low Bay

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00194995069507
Manufacturers Part Number	CSVT L48 ALO3 MVOLT SWW3 80CRI
UPC	194995069507

Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
Type	LOW BAY

Trade Size

aperture size	4FT
---------------	-----

Packaging

Carton	1
Weight Per each	5.2

Uses, Certifications, and Standards

Application	Manufacturing,Parking Garage,Sports and Recreation,Warehouses
environmental conditions	Demanding,Indoor,Outdoor
Mounting	Pendant,Surface,Suspended
standard	CSA,NOMDLC Standard