



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DG132025FBC21C DG1 230V FR2 N1 7.5HP 25A CT 10HP 31A VT W/ BC Eaton Corp

Catalog Number	DG132025FBC21C
Manufacturer	Eaton Corp
Description	Powerxl DG1 Af Drive, 5.5 KW 7.5 HP CT 3-Phase 50/60 HZ 25A Output IP21/Type 1 Enclosure FR2 LCD Display Internal Emc Filter & DC Choke Ethernet, RS-485, Bacnet MS/TP, Modbus TCP & Rtu Ports 2 Expansion Slots Brake Chopper
Weight per unit	29.0 (lbs/each)
Product Category	Ac Drives

Features

display	LCD graphical
Input Voltage	400 V, 380-500 V(-15%, +10%)
keypad	Included

Dimensions and Weight

Depth	28
Height	16
Width	15

Descriptions

Description	DG1 230V FR2 N1 7.5HP 25A CT 10HP 31A VT W/ BC
extra long description	ETN DG1-32025FB-C21C DG1,230V FR2,N
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	PowerXL DG1 AF Drive, 5.5 kW 7.5 Hp CT 3-phase 50/60 Hz 25A output IP21/type 1 enclosure FR2 LCD display Internal EMC filter & DC choke EtherNet, RS-485, BACnet MS/TP, Modbus TCP & RTU ports 2 expansion slots Brake chopper
Product Type	DG1, 230V FR2, N1, 7.5HP, 25A/10HP, 31A, BC
Special Features	Coated board

Manufacturer Information

Brand	Eaton
GTIN	00786685886077
Manufacturers Part Number	DG1-32025FB-C21C
UPC	786685886077



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DRIVES

Type Variable Frequency Drive

Packaging

Carton 1

Weight Per each 29

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

Enclosure IP21/type 1 enclosure

standard UL Listed,EN ISO 13849-1,cUL Listed,IEC 61508,UL 508C,EN
62061,C-Tick Compliant,GoST-R,RoHS Compliant,CE Marked