



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH322NGK 60A/3P HD Fusible Safety Switch W/Neut 240V Nema 1

Eaton Corp

Catalog Number	DH322NGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 60 A, Nema 1, Painted Steel, Class H, Fusible, Neutral, Three-Pole, Four-Wire, 240 V, Max HP: 3, 7.5/ 10, 15/ 10 HP (1, 3PH @STD/TD/250 VDC), #14-#2 Cu/Al
Weight per unit	17.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	60
dimensions	16.5000 IN X 9.5000 IN X 16.0000 IN
Material	Painted Steel
media	Yes
Poles	3
Voltage Rating	240V

### Dimensions and Weight

Depth	16.5
Height	16
Width	9.5

### Descriptions

Description	60A/3P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA 1
extra long description	ETN DH322NGK 60A/3P HD Fusible Sfty
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 60 A, NEMA 1, Painted steel, Class H, Fusible, Neutral, Three-pole, Four-wire, 240 V, Max Hp: 3, 7.5/ 10, 15/ 10 hp (1,3PH @Std/TD/250 Vdc), #14-#2 Cu/Al
Product Type	60A/3P HD Fusible Sfty SW W/Neut 240V N1

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113205823
Manufacturers Part Number	DH322NGK
UPC	782113205823



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... DISCONNECTS

Type ..... Fusible safety switch

## Packaging

Carton ..... 1

Weight Per each ..... 17

## Uses, Certifications, and Standards

Application ..... Commercial / Institutional Buildings / Structures - Power  
Distribution and Controls

nema rating ..... 1

standard ..... UL Listed, NEC 230.62 (C) Compliant Barrier