



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DJ4X1C100 2" Orange Corr W/ Tape Riser-Gard

Abb Installation Products, Inc

Catalog Number	DJ4X1C100
Manufacturer	Abb Installation Products, Inc
Description	Riser-Gard Fiber Optic Corrugated Conduit, Size 2 Inches, Outer Diameter 2.38 Inches, Inner Diameter 2 Inches, Wall Thickness 0.080 Inch, Length 100 Feet, Material PVC, Color Orange, With Pull Tape
Weight per unit	0.2710 (lbs/each)
Product Category	Non-Metallic Raceway & Accy.

Features

Inside Diameter	2
outside diameter	2.38

Material, Color, and Finish

Color	Orange
-------	--------

Dimensions and Weight

Length	1200
--------	------

Descriptions

Description	2" ORANGE CORR W/ TAPE RISER-GARD
extra long description	ABB DJ4X1C-100 2 INCH R/G ORANGE W/
Long Description	Riser-Gard Fiber Optic Corrugated Conduit, Size 2 Inches, Outer Diameter 2.38 Inches, Inner Diameter 2 Inches, Wall Thickness 0.080 Inch, Length 100 Feet, Material PVC, Color Orange, with Pull Tape
Product Type	2 Inch R/G Orange W/Tape
Special Features	UL Listed and is available with tape pre-installed

Manufacturer Information

Brand	Thomas&Betts-Abb Ins Prod
GTIN	00791207203546
Manufacturers Part Number	DJ4X1C-100
UPC	791207203546

Taxonomies, Classifications, and Categories

Category Description	PVC & ENT
Type	Riser-Gard Flexible Raceway

Trade Size

Trade Size	2 Inches
------------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
--------	-----

Weight Per foot	0.271
-----------------	-------

Uses, Certifications, and Standards

Application	Riser-Gard is suitable for use in vertical runs in a shaft or between floors, as well as areas other than the plenum
-------------	--

standard	UL e151168
----------	------------