



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E2PB 5.75X3.25X2.75 N12 2H PB

Hoffman Enclosures, Inc.

| | |
|------------------|--|
| Catalog Number | E2PB |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Pushbutton Enclosures Type 12, 2PBX30.5MM, Gray, Steel |
| Weight per unit | 22.6 (lbs/each) |
| Product Category | Control Station Enclosures |

Features

| | |
|-----------------|------------|
| ip rating | IP65 |
| Material | MILD STEEL |
| Number of Holes | 2 |

Material, Color, and Finish

| | |
|------------|---------------|
| Color | Gray |
| Color Code | ANSI 61 |
| Finish | Powder Coated |

Dimensions and Weight

| | |
|--------|--------------|
| Depth | 2.75 |
| Height | 5.75 |
| Size | 2PB x 30.5mm |
| Width | 3.25 |

Descriptions

| | |
|------------------------|---|
| Description | 5.75X3.25X2.75 N12 2H PB |
| extra long description | NVENT HOF E2PB 2 PB Enclosure 5.75x |
| Features | These pushbutton enclosures are designed to hold 30.5-mm or 22.5-mm pushbuttons and switches. |
| Long Description | Pushbutton Enclosures Type 12, 2PBx30.5mm, Gray, Steel |
| Product Type | 2 PB Enclosure 5.75X3.25X2.75 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510580209 |
| Manufacturers Part Number | E2PB |
| UPC | 783510580209 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | STEEL JUNCTION BOXES |
| Type | Mild Steel Industrial Terminal and Junction Boxes |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 22.56 |

Uses, Certifications, and Standards

| | |
|-------------|---------------------------|
| Application | Controls and Drives |
| nema rating | 12 Indoor, dust-resistant |