



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E50KL552 E50 Operating Lever

Eaton Corp

Catalog Number	E50KL552
Manufacturer	Eaton Corp
Description	E50 Nema Limit Switch, Lever, Rotary Lever, 2.0 Inch Len, Stainless Steel, Ball Bearing Roller 0.69 Inch Diameter 0.25 Inch Width, 14-250F(-10-121C), Stainless Steel, Steel, UL, Csa, Ce
Weight per unit	0.0500 (lbs/each)
Product Category	Limit Switch Arms, Actuators &

Features

dimensions	2.7200 IN X 0.6900 IN X 0.6100 IN
------------	-----------------------------------

Dimensions and Weight

Depth	0.69
Height	0.61
Width	0.69

Descriptions

Description	E50 OPERATING LEVER
extra long description	ETN E50KL552 E50 LS LEVER,SS,BB ROL
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	E50 NEMA Limit Switch,Lever,Rotary lever,2.0 inch len,Stainless steel,Ball Bearing roller 0.69 inch diameter 0.25 inch width,14-250F(-10-121C),Stainless Steel,Steel,UL,CSA,CE
Product Type	E50 LS Lever, SS, BB Roller, 2IN Len
Special Features	Used with Used with side rotary

Manufacturer Information

Brand	Eaton
GTIN	00782113322186
Manufacturers Part Number	E50KL552
UPC	782113322186

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch accessory



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.05

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Operating Temperature	10
standard	UL Listed, CSA Certified, CE, RoHS Compliant, CE Marked