



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DV600PLA Diva 600W SP Ltalmd Lutron

|                  |   |
|------------------|---|
| Catalog Number   | DV600PLA  |
| Manufacturer     | Lutron  |
| Description      | 00027557366281   0027557   027557366281   02755736628   36628   DV 600P La   DV600PLA   DV-600P-La   Diva Inc 600 Watt SGL Pole Preset LT Al   Lewtron Electronics DV 600P La   Lewtron Electronics DV600PLA   Lewtron Electronics DV-600P-La   Lootron Electronics DV 600P La   Lootron Electronics DV600PLA   Lootron Electronics DV-600P-La   Lutron DV 600P La   Lutron DV600PLA   Lutron DV-600P-La   Lutron Electric DV 600P La   Lutron Electric DV600PLA   Lutron Electric DV-600P-La   Lutron Electronics DV 600P La   Lutron Electronics DV600PLA   Lutron Electron |
| Weight per unit  | 0.0800 (lbs/each)   |
| Product Category | Lighting Dimmers  |

### Features

|                 |                  |
|-----------------|------------------|
| actuator        | Paddle Switch    |
| amperage rating | 48.000 48.000    |
| class           | Lighting Control |
| Coil Voltage    | 48.000 48.000    |
| connection      | Wire Leads       |
| insulation      | Plastic          |
| Material        | METAL/PLASTIC    |
| Poles           | 1                |
| Voltage Rating  | 120              |
| Wattage         | 600              |

### Material, Color, and Finish

|       |              |
|-------|--------------|
| Color | Light Almond |
|-------|--------------|

### Dimensions and Weight

|      |                                    |
|------|------------------------------------|
| Size | 4.69 in (119 mm) x 2.94 in (75 mm) |
|------|------------------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                  |  |
|------------------|--|
| Description      | DIVA 600W SP LTALMD  |
| Long Description | 00027557366281   0027557   027557366281   02755736628   36628   DV 600P LA   DV600PLA   DV-600P-LA   DIVA INC 600 WATT SGL POLE PRESET LT AL   Lewtron Electronics DV 600P LA   Lewtron Electronics DV600PLA   Lewtron Electronics DV-600P-LA   Lutron Electronics DV 600P LA   Lutron Electronics DV600PLA   Lutron Electronics DV-600P-LA   Lutron DV 600P LA   Lutron DV600PLA   Lutron DV-600P-LA   LUTRON ELECTRIC DV 600P LA   LUTRON ELECTRIC DV600PLA   LUTRON ELECTRIC DV-600P-LA   LUTRON ELECTRONICS DV 600P LA   LUTRON ELECTRONICS DV600PLA   LUTRON ELECTRON |
| Product Type     | Obsolete-Diva Inc 600W SP Preset LT AI   |
| Special Features | Controls 600 W incandescent or halogen loads. Paddle turns on/off. Slide up to brighten, down to dim.  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Lutron         |
| GTIN                      | 00027557366281 |
| Manufacturers Part Number | DV-600P-LA     |
| sub brand                 | Prevail Series |
| UPC                       | 027557366281   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type                 | Dimmer, single-pole  |

## Availability

|                     |          |
|---------------------|----------|
| Manufacturer Status | Inactive |
| Status              | Inactive |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 12   |
| Weight Per each | 0.08 |

## Uses, Certifications, and Standards

|                                |   |
|--------------------------------|---|
| Application                    | Lighting Control                        |
| Enclosure                      | Plastic                                 |
| Frequency Rating               | 60                                      |
| Mounting                       | WALLBOX                                 |
| Operating Temperature standard | 32 to 104 F (0 to 40 C)<br>UL, CSA, NOM |