



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

CFL is now LED+



Now name and look. Same trusted technology.  
Superior energy savings.  
Longer life expectancy.  
No mercury. No heat. No flicker.  
No need to replace. No need to worry.

## DVCL253PIV Diva 250W Led 3WAY Ivory Lutron

Catalog Number	DVCL253PIV
Manufacturer	Lutron
Description	Diva Gloss Dimmer For 250W CFL/Led, 600W Inc/Hal, or Lutron Hi-Lume A-Series Lte Led Driver In Ivory
Weight per unit	0.3500 (lbs/each)
Product Category	Lighting Dimmers

### Features

actuator	Paddle Switch
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
Poles	1
Switch Type	Paddle Switch
Voltage Rating	120
Wattage	600

### Material, Color, and Finish

Color	Ivory
Finish	Gloss

### Dimensions and Weight

Size	4.69 x 2.94; 119 x 75
------	-----------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	DIVA 250W LED 3WAY IVORY
extra long description	LUT DVCL-253P-IV DIVA CFL/LED BOX 2
Features	The Diva 250-Watt LED+ dimmer switch works with dimmable LED and CFL screw-in bulbs up to 250-Watt and is also compatible with up to 600-Watt of standard incandescent and halogen bulbs, allowing you to control all 4 bulb types on the same circuit. It is designed to control a broad range of dimmable LED and CFL bulbs from a variety of brands including Philips, Cree, GE, EcoSmart and Lighting Science. With the same features as Lutron's Diva dimmer switch, the large paddle switch turns the light on/off and re
Long Description	Diva gloss dimmer for 250W CFL/LED, 600W inc/hal, or Lutron Hi-Lume A-Series LTE LED Driver in ivory
Product Type	Diva CFL/Led Box 250W Ivory
Special Features	Controls 250 W dimmable LED/CFL (screw-base), 600 W incandescent/halogen or 350 W Hi-Lume 1 percent 2-wire LED driver loads. Paddle turns on/off. Slide up to brighten, down to dim. Provides reliable dimming of dimmable LEDs/CFLs, as well as halogens and incandescents.

## Manufacturer Information

Brand	Lutron
GTIN	00784276092029
Manufacturers Part Number	DVCL-253P-IV
UPC	784276092029

## Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer, 3-way/single-pole

## Packaging

Carton	1
Weight Per each	0.35

## Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, CSA, NEMA SSL-7A Type 2