



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E50ANR1 E50 Heavy Duty Limit Switch

Eaton Corp

Catalog Number	E50ANR1
Manufacturer	Eaton Corp
Description	E50 Nema Limit Switch, Side Rotary, Standard Spring Ret, Neon, 14-250F(-10-121C), 1NO-1NC, 10A@240VAC, 1A@250VDC, Mech 10M Elec 1M Cy Full Load, 8000 Cy/HR, Screw Term, 1/2NPT Cond, Nema 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, Diec ZN, UI, Csa, Ce
Weight per unit	0.4100 (lbs/each)
Product Category	Heavy Duty Limit Switches

Features

actuator	Side rotary
connection	Screw Terminal
Contact Configuration	1 NO-1 NC
Contact Rating	10A at 12 Vac, 1A at 125 Vdc
dimensions	4.2200 IN X 1.5400 IN X 2.2500 IN

Descriptions

Description	E50 HEAVY DUTY LIMIT SWITCH
extra long description	ETN E50ANR1 NEMA LIMIT SWITCH,SIDE
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	E50 NEMA Limit Switch,Side Rotary,Standard Spring Ret,Neon,14-250F(-10-121C),1NO-1NC,10A@240Vac,1A@250Vdc,Mech 10M Elec 1M cy full load,8000 cy/hr,Screw term,1/2NPT cond,NEMA 1,3,3S,4,4X,6,6P,13,IP67,Diec Zn,UL,CSA,CE
Product Type	Nema Limit Switch, Side Rotary, Nonc, Neon

Manufacturer Information

Brand	Eaton
GTIN	00782113308845
Manufacturers Part Number	E50ANR1
UPC	782113308845



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch

Packaging

Carton	1
Weight Per each	0.41

Uses, Certifications, and Standards

Application	Water and Wastewater Systems - Water and Wastewater Systems - Other Stationary Mach Equip In Factory - Machine Tools: Cutting Stationary Mach Equip In Factory - Machine Tools: Forming Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL Listed, CSA Certified, RoHS Compliant, CE Marked