



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ECNR35 35A 250V Class RK5 Time Delay CL Fuse

Edison Fuses

Catalog Number	ECNR35
Manufacturer	Edison Fuses
Description	Time Delay Power Fuse, RK5 Class Fuse, Ferrule Fuse, 10 S @ 500% Response Time, Ferrule End X Ferrule End Connection, 35 A, 250 V Ac;125 V DC, Ferrule Terminal, 0.81 In Diameter, 3 In Overall Length, 1 LB
Weight per unit	0.1200 (lbs/each)
Product Category	Dual Element

Features

Characteristics	Dual Element, 10 Second Time Delay
Interrupting Rating	200000 Amp (DC)

Dimensions and Weight

Length	3 INCH
--------	--------

Descriptions

Additional Information	Application General-Purpose Including Lighting, Heating and Other Non-Inductive Load
Commodity Description	DUAL ELEMENT FUSES
Description	35A 250V CLASS RK5 TIME DELAY CL FUSE
extra long description	CLASS RK5 TYPE; 3 INCH; UL 248-12, CE, CSA C22.2 APPROVAL; 250 VOLT AC/125 VOLT DC VOLTAGE RATING; 0.81 INCH DIAMETER; 200000 AMP (DC) INTERRUPTING RATING; 35 AMP CURRENT RATING; FERRULE TERMINAL TYPE; DUAL ELEMENT, 10 SECOND TIME DELAY CHARACTERISTICS; EDISON BRAND; APPLICATION GENERAL-PURPOSE INCLUDING LIGHTING, HEATING AND OTHER NON-INDUCTIVE LOAD; ECNR MODEL

Manufacturer Information

Brand	EDISON
GTIN	00782634507352
Model	ECNR
UPC	782634507352

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	CLASS RK5

Availability

Manufacturer Status	Non-Stock
---------------------	-----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.12

Uses, Certifications, and Standards

Approval	UL 248-12, CE, CSA C22.2
----------	--------------------------