



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EMH25D31GSKM15 3P PB Manual Starter

*Crouse-Hinds*

Catalog Number	EMH25D31GSKM15
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Emn Nema Manual Pushbutton Starter, With Starter, 7.5 HP/10 HP, Square D Starter, Copper-Free Aluminum, Nema Size 1, Three-Pole, Polyphase, 200-230 Vac/380-575 Vac, Gasket, M15 Model
Weight per unit	14.2 (lbs/each)
Product Category	Controls

### Features

motor power	7.5-10 HP
Phase	3 Ph
Poles	3
Voltage Rating	200-230 Vac/380-575 Vac

### Dimensions and Weight

Depth	7.94
Height	10.44
Size	10.44 x 7.94 x 7.80
Width	7.6

### Descriptions

Description	3P PB MANUAL STARTER
extra long description	CRS-H EMN25 D31 GSK M15 MAN STARTER
Features	Crouse-Hinds series EMN pushbutton style compact manual NEMA starters are used on drilling rigs or mud agitators and shakers where flammable or explosive gases are present. Also used for fans and blowers, pumps, compressors and conveyors.
Long Description	Eaton Crouse-Hinds series EMN NEMA manual pushbutton starter, With starter, 7.5 HP/10 HP, Square D starter, Copper-free aluminum, NEMA size 1, Three-pole, Polyphase, 200-230 Vac/380-575 Vac, Gasket, M15 model
Product Type	Man Starter NEMA7 PB 3P Size 1 SQ D GSK
Special Features	Gasket

### Manufacturer Information

Brand	Eaton
GTIN	00662276571143
Manufacturers Part Number	EMN25 D31 GSK M15
UPC	662276571143



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... 1PH MANUAL STARTERS

## Availability

Status ..... Inactive

## Packaging

Carton ..... 1

Weight Per each ..... 14.1699

## Uses, Certifications, and Standards

Application ..... Ind Facilities & Factories - Facility: Power Distribution and Control

Enclosure ..... Cast Aluminum

environmental conditions ..... where flammable, explosive gases present

Mounting ..... WALL MOUNT

standard ..... CSA Certified ,UL Listed