



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EN1450 14" Enclosure W/Hinged Cover + Lock

*Pass & Seymour/Legrand*

Catalog Number	EN1450
Manufacturer	Pass & Seymour/Legrand
Description	<P>This 14"" Enclosure Features Universal On-Q Bay-Style Mounting Holes That Are Compatible With All Bay-Style Modules. It Also Includes Larger Top Openings That Make Pulling Wire Easier As Well As Additional Knockouts, More Side Lances, and Side Tabs For
Weight per unit	9.8 (lbs/each)
Product Category	Enclosures & Cabinets

### Features

Cable Entry	(6) rear knockouts
Enclosure Size	14.0
face plate	Hinged Cover and Lock
frame	Cold Rolled Steel
Material	Steel

### Material, Color, and Finish

Color	White
Finish	Powder Coat

### Dimensions and Weight

Depth	3.7"
Height	14.1"
Thickness	0.1
Width	14.3"

### Descriptions

Description	14" ENCLOSURE W/HINGED COVER + LOCK
extra long description	OnQ EN1450 14 ENCL W/HINGED COVER +
Long Description	<p>This 14"" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for
Product Type	14 Encl W/Hinged Cover + Lock
Special Features	Flanged covers hide drywall openings- Flush and surface-mounted- Mounting tabs provide correct flush-mount position



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Legrand On-Q
GTIN	00804428023036
Manufacturers Part Number	EN1450
UPC	804428023036

## Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	ENCLOSURE

## Packaging

Carton	1
Weight Per each	9.75

## Uses, Certifications, and Standards

Application	Residential
Mounting standard	Surface or Flush UL, ROHS, CULUS, CSA, UL (UL985, UL1023, UL1863), cULus, CSA, RoHS