



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **ESX1LEDP450KR5MV \*Delisted\* ESX1 Led P4 50K R5 Mvolt Upa BLS DDBXD** *Lithonia Lighting - Acuity*

Catalog Number	ESX1LEDP450KR5MV
Manufacturer	Lithonia Lighting - Acuity
Description	Lith ESX1 Led P4 50K R5 Mvolt Upa B
Weight per unit	11.7 (lbs/each)
Product Category	Lighting

### Features

average life	60,000
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	21,000 LM,22,000 LM,23,000 LM,24,000 LM,25,000 LM
Material	Aluminum
Maximum Operating Temperature	40
media	Yes
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Wattage	200

### Material, Color, and Finish

Color	Bronze
color rendering index (cri)	70
color temperature	5000
Finish	Gloss
Lens Color	Clear
Lens Material	Glass
Style	CONTEMPORARY

### Dimensions and Weight

Height	2.87
Length	19.94
Width	12

### Descriptions

Description	*DELISTED* ESX1 LED P4 50K R5 MVOLT UPA BLS DDBXD
Long Description	LITH ESX1 LED P4 50K R5 MVOLT UPA B
Product Type	Area Light



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00194994838548
Manufacturers Part Number	ESX1 LED P4 50K R5 MVOLT UPA B
UPC	194994838548

## Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
----------------------	--

## Availability

Manufacturer Status	Inactive
---------------------	----------

## Packaging

Carton	1
Package	2
Weight Per each	11.73

## Uses, Certifications, and Standards

Application	Automotive & Parking, Offices & Banks, Retail
environmental conditions	OUTDOOR
Mounting	Arm Mount, Surface
standard	C-UL-USDLC Premium, Nighttime Friendly