

## DESCRIPTION

White reflector trim in the 6" All-Pro trim family for use in Halo and All-Pro recessed downlighting.

Catalog #		Type
Project		
Comments		Date
Prepared by		

## SPECIFICATION FEATURES

Socket supporting trim, available in high gloss appliance white with white reflector. TS version uses torsion springs to hold trim tight to ceiling.

### Lamp Listings - GU24

H724ICAT	CF15/R30/GU24
H724ICATL	
H724RICAT	CF13/GU24 (spiral)
H724RICATL	

### Lamp Listings - Incandescent

ET700	85W BR30, 120W BR40, 100W R30, 75W PAR30L, 100W A19
ET700R	65W BR30, 75W PAR30L

EI700	40W A19, 65W BR30, 75W PAR30, 75W PAR30L, 75W R30, 90W BR40
EI700AT	
EI700ATNB	
EI700NB	
EI700R	
EI700RAT	


EI700U	60W A19, 75W PAR30, 75W PAR30L, 85W BR30, 100W R30, 120W BR40
EI700UAT	




**ERT712**  
Gloss White Trim,  
White Reflector



**ERT712TS**  
Gloss White Trim, White  
Reflector and Torsion Spring



**ERT712**  
Height: 5-3/8" [136mm]  
Outside Diameter: 7-1/4" [184mm]




**ERT712TS**  
Height: 5-3/8" [136mm]  
Outside Diameter: 7-1/4" [184mm]

## ERT712

6-Inch White Reflector

## ORDERING INFORMATION

Trim



**ERT712** = 6" High gloss appliance white trim with white reflector  
**ERT712TS** = 6" High gloss appliance white trim with white reflector, torsion spring

## DESCRIPTION

White reflector trim in the 6" All-Pro trim family for use in Halo and All-Pro recessed downlighting.

Catalog #		Type
Project		
Comments		Date
Prepared by		

## SPECIFICATION FEATURES

Socket supporting trim, available in high gloss appliance white with white reflector. TS version uses torsion springs to hold trim tight to ceiling.

### Lamp Listings - GU24

H724ICAT	CF15/R30/GU24
H724ICATL	
H724RICAT	CF13/GU24 (spiral)
H724RICATL	

### Lamp Listings - Incandescent

ET700	85W BR30, 120W BR40, 100W R30, 75W PAR30L, 100W A19
ET700R	65W BR30, 75W PAR30L

EI700	40W A19, 65W BR30, 75W PAR30, 75W PAR30L, 75W R30, 90W BR40
EI700AT	
EI700ATNB	
EI700NB	
EI700R	
EI700RAT	


EI700U	60W A19, 75W PAR30, 75W PAR30L, 85W BR30, 100W R30, 120W BR40
EI700UAT	




**ERT712**  
Gloss White Trim,  
White Reflector



**ERT712TS**  
Gloss White Trim, White  
Reflector and Torsion Spring



**ERT712**  
Height: 5-3/8" [136mm]  
Outside Diameter: 7-1/4" [184mm]




**ERT712TS**  
Height: 5-3/8" [136mm]  
Outside Diameter: 7-1/4" [184mm]

## ERT712

6-Inch White Reflector

## ORDERING INFORMATION

Trim



**ERT712** = 6" High gloss appliance white trim with white reflector  
**ERT712TS** = 6" High gloss appliance white trim with white reflector, torsion spring