



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EZ10168362K E-Z1016 M P DSS 2/0 to 4/0 BK Kit *Crouse-Hinds*

Catalog Number	EZ10168362K
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Cam-Lok J Series E-Z1016 Plug, Up to 400A Continuous, 2/0-4/0 Awg, Black, Double Set Screw, Brass Contacts, Male, Thermoplastic Elastomer (Tpe), Single Packaged Unit, Non-Vulcanized, 600 Vac/DC
Weight per unit	1.0 (lbs/each)
Product Category	Wiring Devices

Features

amperage rating	400
connection	Double Set Screw
dimensions	7.1400 IN X 1.4900 IN X 1.4900 IN
Poles	1
Voltage Rating	600 V
Wire Size	2 To 4/0 AWG

Dimensions and Weight

Size	1.49 In Diameter X 7.14 In Length
------	-----------------------------------

Descriptions

Description	E-Z1016 M P DSS 2/0 TO 4/0 BK KIT
extra long description	CRS-H E-Z1016-8362K E-Z1016 M P DSS
Features	The Cam-Lok J series from Eaton's Crouse-Hinds Division provides the means to quickly connect and disconnect power systems safely. Cam-Lok is the industry standard for motors, generators, indoor and outdoor lighting distribution panels, and numerous other power applications.
Long Description	Eaton Crouse-Hinds series Cam-Lok J Series E-Z1016 plug, Up to 400A continuous, 2/0-4/0 AWG, Black, Double set screw, Brass contacts, Male, Thermoplastic elastomer (TPE), Single packaged unit, Non-vulcanized, 600 Vac/dc
Product Type	E-Z1016 M P DSS 2/0 to 4/0 BK Kit
Special Features	NEMA 3R/4 Enclosure

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662275868473
Manufacturers Part Number	E-Z1016-8362K
UPC	662275868473



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	PLUG

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
environmental conditions	-40 To 105 Deg C
standard	UL, CSA