



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EZ10168391 2/0-4/0 GRN FM Plug

*Crouse-Hinds*

Catalog Number	EZ10168391
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Cam-Lok J Series E-Z1016 Plug, Up to 400A Continuous, 2/0-4/0 Awg, Green, Double Set Screw, Brass Contacts, Female, Thermoplastic Elastomer (Tpe), Non-Vulcanized, 600 Vac/DC
Weight per unit	1.0 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	400
connection	Double Set Screw
dimensions	7.2600 IN X 1.4900 IN X 1.4900 IN
Poles	1
Voltage Rating	600 V
Wire Size	2 To 4/0 AWG

### Dimensions and Weight

Size	1.49 In Diameter X 7.26 In Length
------	-----------------------------------

### Descriptions

Description	2/0-4/0 GRN FM PLUG
extra long description	CRS-H E-Z1016-8391 E-Z1016 F P DSS
Features	The Cam-Lok J series from Eaton's Crouse-Hinds Division provides the means to quickly connect and disconnect power systems safely. Cam-Lok is the industry standard for motors, generators, indoor and outdoor lighting distribution panels, and numerous other power applications.
Long Description	Eaton Crouse-Hinds series Cam-Lok J Series E-Z1016 plug, Up to 400A continuous, 2/0-4/0 AWG, Green, Double set screw, Brass contacts, Female, Thermoplastic elastomer (TPE), Non-vulcanized, 600 Vac/dc
Product Type	E-Z1016 F P DSS 2/0 to 4/0 GR
Special Features	NEMA 3R/4 Enclosure

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662275120793
Manufacturers Part Number	E-Z1016-8391
UPC	662275120793



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	PLUG

## Packaging

Carton	1
Weight Per each	1

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
environmental conditions	-40 To 105 Deg C
standard	UL, CSA