




GE
Lighting

66349 - F32T8/SPP41/ECO

F32T8/SPP41/ECO-LFL PULP TRY PK NEW COLOR TEMP



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
Bulb	Linear
Base	T8
Rated Life	Medium Bi-Pin (G13)
Rated Life (instant start) @ Time	30000.0 hrs
Rated Life (rapid start) @ Time	18000 h @ 3 h
	24000 h @ 12 h
	30000.0 @ 3.0/36000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
LEED-EB MR Credit	36 picograms Hg per mean lumen hour
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	2900.0
Mean Lumens	2725.0
Nominal Initial Lumens per Watt	90
Color Temperature	4100.0 K
Color Rendering Index (CRI)	80.0

ELECTRICAL CHARACTERISTICS

Wattage	32.0
---------	------

DIMENSIONS

Maximum Overall Length (MOL)	48.0000 in(1219.2 mm)
Nominal Length	48.000 in(1219.2 mm)
Bulb Diameter (DIA)	1.000 in(25.4 mm)

PRODUCT INFORMATION


Product Code	66349
Description	F32T8/SPP41/ECO
Standard Package	Case
Standard Package GTIN	10043168663493
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168663496



GE
Lighting

66349 - F32T8/SPP41/ECO

F32T8/SPP41/ECO-LFL PULP TRY PK NEW COLOR TEMP



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
Bulb	Linear
Base	T8
Rated Life	Medium Bi-Pin (G13)
Rated Life (instant start) @ Time	30000.0 hrs
Rated Life (rapid start) @ Time	18000 h @ 3 h
	24000 h @ 12 h
	30000.0 @ 3.0/36000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
LEED-EB MR Credit	36 picograms Hg per mean lumen hour
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	2900.0
Mean Lumens	2725.0
Nominal Initial Lumens per Watt	90
Color Temperature	4100.0 K
Color Rendering Index (CRI)	80.0

ELECTRICAL CHARACTERISTICS

Wattage	32.0
---------	------

DIMENSIONS

Maximum Overall Length (MOL)	48.0000 in(1219.2 mm)
Nominal Length	48.000 in(1219.2 mm)
Bulb Diameter (DIA)	1.000 in(25.4 mm)

PRODUCT INFORMATION

Product Code	66349
Description	F32T8/SPP41/ECO
Standard Package	Case
Standard Package GTIN	10043168663493
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168663496