



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F42T12CWHO \*Delisted\* 55W T12 Ho Cool White

*Sylvania-Ledvance*

|                  |  |
|------------------|--|
| Catalog Number   | F42T12CWHO   |
| Manufacturer     | Sylvania-Ledvance  |
| Description      | OBS25342 55W, 42" Mol, T12 Ho (800 Ma) Rapid Start<br>Fluorescent Lamp, Cool Whitephosphor, 4200K Color<br>Temperature, 60 Cri |
| Weight per unit  | 0.6200 (lbs/each)  |
| Product Category | Linear Fluorescent Straight La   |

### Features

|                           |                                     |
|---------------------------|-------------------------------------|
| amperage rating           | Ballast Dependent                   |
| average life              | 9000                                |
| Base                      | Recessed Double Contact             |
| lumens                    | 3400 Initial Lumens at 25 Degrees C |
| Shape                     | T12                                 |
| start type                | Rapid Start                         |
| total harmonic distortion | Ballast Dependent                   |
| Voltage Rating            | Ballast Dependent                   |
| Wattage                   | 55                                  |

### Material, Color, and Finish

|                             |                 |
|-----------------------------|-----------------|
| color rendering index (cri) | 60              |
| color temperature           | 4200            |
| Finish                      | Phosphor Coated |

### Dimensions and Weight

|          |        |
|----------|--------|
| Diameter | 1.5 in |
|----------|--------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | *DELISTED* 55W T12 HO COOL WHITE   |
| extra long description | SYL F42T12/CW/HO/25342 F42T12CWHO 3  |
| Long Description       | OBS25342 55W, 42" MOL, T12 HO (800 mA) rapid start<br>fluorescent lamp, Cool Whitephosphor, 4200K color<br>temperature, 60 CRI |
| Product Type           | F42T12CWHO 30/CS 1/Sku   |
| Special Features       | COOL WHITE   |

### Manufacturer Information

|                           |                    |
|---------------------------|--------------------|
| Brand                     | SYLVANIA           |
| GTIN                      | 00046135253423     |
| Manufacturers Part Number | F42T12/CW/HO/25342 |
| UPC                       | 046135253423       |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fluorescent

Type ..... FLUORESCENT

## Packaging

Carton ..... 1

Package ..... 30

Weight Per each ..... 0.62

## Uses, Certifications, and Standards

Application ..... Commercial/Residential