




GE  
Lighting

**68871 - F96T8/XL/SPX50/2**  
F96T8/XL/SPX50/2



**GENERAL CHARACTERISTICS**

Lamp Type	Linear Fluorescent - Straight
Bulb	Linear
Base	T8
Rated Life (NOM)	Single Pin (Fa8)
Bulb Material	24000.0 h
Starting Temperature (MIN)	Sodalime glass
Mercury Content (NOM)	10.0 °C
Picograms of Mercury (NOM)	90.0 mg
Primary Application	663.7168 pg
	Full Wattage

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens (NOM)	5950.0
Mean Lumens (NOM)	5650.0
Nominal Initial Lumens per Watt (NOM)	100.8475
Color Temperature (NOM)	5000.0 K
Color Rendering Index (CRI) (NOM)	82.0

**ELECTRICAL CHARACTERISTICS**

Wattage (NOM)	59.0
---------------	------

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	96.000 in(2438.4 mm)
Nominal Length (NOM)	96.000 in(2438.4 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)


**PRODUCT INFORMATION**

Product Code	68871
Description	F96T8/XL/SPX50/2
Standard Package	Case
Standard Package GTIN	10043168688717
Standard Package Quantity	24
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	24
UPC	043168688710



GE  
Lighting

**68871 - F96T8/XL/SPX50/2**  
F96T8/XL/SPX50/2



**GENERAL CHARACTERISTICS**

Lamp Type	Linear Fluorescent - Straight
Bulb	Linear
Base	T8
Rated Life (NOM)	Single Pin (Fa8)
Bulb Material	24000.0 h
Starting Temperature (MIN)	Sodalime glass
Mercury Content (NOM)	10.0 °C
Picograms of Mercury (NOM)	90.0 mg
Primary Application	663.7168 pg
	Full Wattage

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens (NOM)	5950.0
Mean Lumens (NOM)	5650.0
Nominal Initial Lumens per Watt (NOM)	100.8475
Color Temperature (NOM)	5000.0 K
Color Rendering Index (CRI) (NOM)	82.0

**ELECTRICAL CHARACTERISTICS**

Wattage (NOM)	59.0
---------------	------

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	96.000 in(2438.4 mm)
Nominal Length (NOM)	96.000 in(2438.4 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

**PRODUCT INFORMATION**

Product Code	68871
Description	F96T8/XL/SPX50/2
Standard Package	Case
Standard Package GTIN	10043168688717
Standard Package Quantity	24
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	24
UPC	043168688710