



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **FD3015 Type FD BRKR 3P 15A 600VAC Max 18K Aic** *Eaton Corp*

|                  |                                                                                                                                                                                      |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | FD3015                                                                                                                                                                               |
| Manufacturer     | Eaton Corp                                                                                                                                                                           |
| Description      | Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, FD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Three-Pole, 15 A, 600 Vac, 250 VDC, Load Side, 50/60 HZ |
| Weight per unit  | 5.0 (lbs/each)                                                                                                                                                                       |
| Product Category | 3 Pole                                                                                                                                                                               |

### **Features**

|                |                                   |
|----------------|-----------------------------------|
| Current Rating | 15 A                              |
| dimensions     | 3.3800 IN X 4.1300 IN X 6.0000 IN |
| frame          | F                                 |
| media          | Yes                               |
| Poles          | 3                                 |
| Voltage Rating | 600 VAC, 250 VDC                  |

### **Descriptions**

|                        |                                                                                                                                                                                                                                                                                                                                                                                                           |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | TYPE FD BRKR 3P 15A 600VAC MAX 18K AIC                                                                                                                                                                                                                                                                                                                                                                    |
| extra long description | ETN FD3015 TYPE FD BRK 3P 15A 600VA                                                                                                                                                                                                                                                                                                                                                                       |
| Features               | Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A. |
| Long Description       | Eaton Series C complete molded case circuit breaker, F-frame, FD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 15 A, 600 Vac, 250 Vdc, Load side, 50/60 Hz                                                                                                                                                                                                                      |
| Product Type           | Type FD BRK 3P 15A 600VAC Max 18K Aic                                                                                                                                                                                                                                                                                                                                                                     |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786679305607 |
| Manufacturers Part Number | FD3015         |
| UPC                       | 786679305607   |

### **Taxonomies, Classifications, and Categories**

|                      |                             |
|----------------------|-----------------------------|
| Category Description | MOLDED CASE BREAKERS        |
| Type                 | Molded case circuit breaker |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |   |
|-----------------|---|
| Carton          | 1 |
| Weight Per each | 5 |

## Uses, Certifications, and Standards

|             |                                                                           |
|-------------|---------------------------------------------------------------------------|
| Application | Elec Assemblies, Panels & OEM - Electrical Assemblies and<br>OEMs - Other |
| standard    | UL Listed                                                                 |