



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FDB3125L Type FDB 3 Pole 125A Trip 600V Class Line and Load

Eaton Corp

Catalog Number	FDB3125L
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, FDB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Three-Pole, 125A, 600 Vac, 250 VDC, 18 Kaic At 240 Vac, 14 Kaic At 480 Vac, Line and Load, 50/60 HZ
Weight per unit	4.3 (lbs/each)
Product Category	3 Pole

Features

Current Rating	125 A
dimensions	7.4000 IN X 5.0000 IN X 4.9000 IN
frame	F
media	Yes
Poles	3
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	TYPE FDB 3 POLE 125A TRIP 600V CLASS LINE AND LOAD
extra long description	ETN FDB3125L FDB 3P 125A TRIP, 600V
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, FDB, Complete breaker, Fixed thermal, fixed magnetic trip type, Three-pole, 125A, 600 Vac, 250 Vdc, 18 kAIC at 240 Vac, 14 kAIC at 480 Vac, Line and load, 50/60 Hz
Product Type	FDB 3P 125A Trip, 600V Class, Line&Load

Manufacturer Information

Brand	Eaton
GTIN	00786679306055
Manufacturers Part Number	FDB3125L
UPC	786679306055

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	4.3499

Uses, Certifications, and Standards

Application	Other
standard	UL Listed