


**NEW!**  
more on reverse

# Floor Box and Covers for New Concrete

## Non-Metallic Concrete Box • Metal and Plastic Cover Kits



**NON-METALLIC FLOOR BOX**



FLBC4500  
with mud cover in place

Box without mud cover



**COVER KITS FOR BOX**

PLASTIC COVERS  
in 5 COLORS

**NEW!**



FLB6230MB  
WITH METAL COVER

FLBT6615NL  
TRAPDOOR COVER

Brass Trapdoor style  
FLBT6615MB  
(open and back)

Arlington's cost-effective **FLOOR BOX KITS** offer installers the low cost, convenient way to install a receptacle flush with the floor wherever your customer needs one.

Arlington's FLOOR BOX and COVER KITS **FOR NEW CONCRETE** offer flexibility and convenience.


Made of heavy-duty plastic, our 4.5" non-metallic **concrete box** is a common size, that accommodates our 6" round covers as well as most other round covers on the market.

Our versatile concrete box covers are available with flip lids or threaded plugs in brass or nickel-plated brass. **And NOW plastic, in five colors, including paintable white!**

They offer easy installation of receptacles so they'll look great wherever they're installed!

For the **fastest** installation, our trapdoor covers ship **ready to use** with a pre-installed gasket and decorator-style receptacle.

A selection of leveling rings and adapters allows our covers to fit our boxes and most other manufacturers' concrete boxes.



**A**  
**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517  
**800/233.4717**  
**Fax 570/562.0646**  
[www.aifittings.com](http://www.aifittings.com)

# Non-Metallic Floor Box and Cover Kits

*Put a Receptacle in New Concrete – The Easy, Low Cost Way!*




CATALOG NUMBER	UPC/DCI/NAED MFG. #018997	DESCRIPTION FINISH/COLOR, COVER STYLE	NOTES	UNIT PKG	STD PKG
FLBC4500	22010	4.5" Non-metallic <b>ROUND BOX</b> for Concrete Pours (conduit plugs, mud cover)		1	5

## FLB6230MB

Includes brass cover with flip lids, gaskets, receptacle.

Also available with threaded plugs (not shown)



## METAL COVER KITS

FLB6230MB	22025	COVER KIT 6" Round, Brass w two flip lids	* hole pattern fits FLBC4500LR	1	10
FLB6230NL	22026	COVER KIT 6" Round, Nickel-plated w two flip lids	* hole pattern fits FLBC4500LR	1	10
FLB6220MB	22021	COVER KIT 6" Round, Brass w two threaded plugs	* hole pattern fits FLBC4500LR	1	10
FLB6220NL	22022	COVER KIT 6" Round, Nickel-plated w two threaded plugs	* hole pattern fits FLBC4500LR	1	10

## LEVELING RING

FLBC4500LR	22011	Leveling Ring for Arlington FLBC4500 and round metal covers above (bosses for cover mounting)		1	10
------------	-------	---	--	---	----



## COVER KIT COMPONENTS

## PLASTIC COVER KITS

FLBC4520LA	09674	COVER KIT 6" Round, LIGHT ALMOND – Plastic gasketed cover, mounting plate, leveling ring		1	10
FLBC4520W	13838	COVER KIT 6" Round, WHITE – Plastic gasketed cover, mounting plate, leveling ring		1	10
FLBC4520GY	09673	COVER KIT 6" Round, GRAY – Plastic gasketed cover, mounting plate, leveling ring		1	10
FLBC4520BR	09672	COVER KIT 6" Round, BROWN – Plastic gasketed cover, mounting plate, leveling ring		1	10
FLBC4520CA	09669	COVER KIT 6" Round, CAMEL – Plastic gasketed cover, mounting plate, leveling ring		1	10



FLBT6615MB closed

FLBT6615NL open



FLBT6615MB open on FLBC4500 concrete box

## TRAPDOOR STYLE, METAL COVERS, LEVELING RING

FLBT6615MB	22030	Trapdoor Cover Round, Brass. Pre-mounted gasket & decorator-style 15A receptade		1	10
FLBT6615NL	22031	Trapdoor Cover Round, Nickel-plated. Pre-mounted gasket & decorator-style 15A receptade		1	10
FLBT6615LR	22029	Leveling Ring for Arlington FLBC4500 box w FLBT6615 trapdoor style cover		1	10

FLBT6615LR



## ADAPTERS

FLBC4500AR	22004	Oversized Adapter Ring for 5" diameter concrete boxes		1	10
FLBC4500Y	22012	"Y" Adapter - Provides (2) 1" openings for conduit entering 1" hub		1	10



FLBC4500AR Oversized



FLBC4500Y "Y"



1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
www.aifittings.com

Distributed by

Patents pending Floor Box 0415/15M




PLASTIC COVERS in 5 COLORS

FLBC4520LA closed

**NEW!**  
more on  
reverse

# Floor Box and Covers for New Concrete

## Non-Metallic Concrete Box • Metal and Plastic Cover Kits



**NON-METALLIC  
FLOOR  
BOX**



FLBC4500  
with mud cover in place

Box without mud cover



**COVER KITS FOR BOX**

PLASTIC COVERS  
in 5 COLORS

**NEW!**

Arlington's cost-effective **FLOOR BOX KITS** offer installers the low cost, *convenient* way to install a receptacle flush with the floor wherever your customer needs one.

Arlington's FLOOR BOX and COVER KITS **FOR NEW CONCRETE** offer flexibility and convenience.


Made of heavy-duty plastic, our 4.5" non-metallic **concrete box** is a common size, that accommodates our 6" round covers as well as *most other round covers on the market*.

Our versatile concrete box covers are available with flip lids or threaded plugs in brass or nickel-plated brass. **And NOW plastic, in five colors, including paintable white!**

They offer easy installation of receptacles so they'll look great wherever they're installed!

For the *fastest* installation, our trapdoor covers ship *ready to use* with a pre-installed gasket and decorator-style receptacle.

A selection of leveling rings and adapters allows our covers to fit our boxes *and* most other manufacturers' concrete boxes.



FLBT6615NL  
**TRAPDOOR COVER**

FLB6230MB  
**WITH METAL COVER**

Brass Trapdoor style  
FLBT6615MB  
(open and back)

# Arlington

1 Stauffer Industrial Park  
Scranton, PA 18517  
**800/233.4717**  
**Fax 570/562.0646**  
[www.aifittings.com](http://www.aifittings.com)

# Non-Metallic Floor Box and Cover Kits

*Put a Receptacle in New Concrete – The Easy, Low Cost Way!*



CATALOG NUMBER	UPC/DCI/NAED MFG. #018997	DESCRIPTION FINISH/COLOR, COVER STYLE	NOTES	UNIT PKG	STD PKG
FLBC4500	22010	4.5" Non-metallic <b>ROUND BOX</b> for Concrete Pours (conduit plugs, mud cover)		1	5

## FLB6230MB

Includes brass cover with flip lids, gaskets, receptacle.

Also available with threaded plugs (not shown)



(available nickel-plated)



## METAL COVER KITS

FLB6230MB	22025	COVER KIT 6" Round, Brass w two flip lids	* hole pattern fits FLBC4500LR	1	10
FLB6230NL	22026	COVER KIT 6" Round, Nickel-plated w two flip lids	* hole pattern fits FLBC4500LR	1	10
FLB6220MB	22021	COVER KIT 6" Round, Brass w two threaded plugs	* hole pattern fits FLBC4500LR	1	10
FLB6220NL	22022	COVER KIT 6" Round, Nickel-plated w two threaded plugs	* hole pattern fits FLBC4500LR	1	10

## LEVELING RING

FLBC4500LR	22011	Leveling Ring for Arlington FLBC4500 and round metal covers above (bosses for cover mounting)		1	10
------------	-------	---	--	---	----



**COVER KIT COMPONENTS**

## PLASTIC COVER KITS

FLBC4520LA	09674	COVER KIT 6" Round, LIGHT ALMOND – Plastic gasketed cover, mounting plate, leveling ring		1	10
FLBC4520W	13838	COVER KIT 6" Round, WHITE – Plastic gasketed cover, mounting plate, leveling ring		1	10
FLBC4520GY	09673	COVER KIT 6" Round, GRAY – Plastic gasketed cover, mounting plate, leveling ring		1	10
FLBC4520BR	09672	COVER KIT 6" Round, BROWN – Plastic gasketed cover, mounting plate, leveling ring		1	10
FLBC4520CA	09669	COVER KIT 6" Round, CAMEL – Plastic gasketed cover, mounting plate, leveling ring		1	10



FLBT6615MB closed



FLBT6615NL open



FLBT6615MB open on FLBC4500 concrete box

## TRAPDOOR STYLE, METAL COVERS, LEVELING RING

FLBT6615MB	22030	Trapdoor Cover Round, Brass. Pre-mounted gasket & decorator-style 15A receptade		1	10
FLBT6615NL	22031	Trapdoor Cover Round, Nickel-plated. Pre-mounted gasket & decorator-style 15A receptade		1	10
FLBT6615LR	22029	Leveling Ring for Arlington FLBC4500 box w FLBT6615 trapdoor style cover		1	10

FLBT6615LR



## ADAPTERS

FLBC4500AR	22004	Oversized Adapter Ring for 5" diameter concrete boxes		1	10
FLBC4500Y	22012	"Y" Adapter - Provides (2) 1" openings for conduit entering 1" hub		1	10



FLBC4500AR Oversized



FLBC4500Y "Y"



**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
www.aifittings.com

© 2015 Arlington Industries, Inc.

Distributed by

Patents pending Floor Box 0415/15M

