

Countertop Box Kits



with Round Stainless Steel Trapdoor Covers



FLBT4465USS



FLBT4465GSS



FLBT4465SS



Cover Closed

Easy to install



1 Determine box location. Cut a 4- 7/16" square opening in countertop. Insert box, bending the clip as necessary to go through opening.



2 Secure box to countertop by tightening two #10 screws inside box...



UNDERSIDE of COUNTER

3 ...drawing the box securely against the underside of the counter. NO GLUING!



4 Wire receptacle in accordance with National, State and local codes.



5 Install trapdoor coverplate to box using the two #6-32 screws provided.
Note: Round cover hides miscut openings

Secure
'NO GLUE'
Installation

Arlington's **Countertop BOX KITS** with round covers give you *lots of options* for installing a device in a countertop.

Get your kit with an installed UL Listed tamper and weather resistant (TWR) decorator-style GFCI... Or tamper resistant (TR) receptacle... OR a combo with (TR) receptacle and two USB ports!

The gasketed, stainless steel **ROUND TRAPDOOR COVERS** look great! They close flush with the countertop, providing 'ingress protection' and preventing damage to the devices in the box. The round shape also covers a miscut opening.

Easy, secure installation

A spring clip holds the box securely against the surface when the screws are tightened. The clip is also 'bendable' so it's easy to insert into the opening in the countertop

- Fits granite or other countertop material up to 1-1/2" thick
- Easy 'No Glue' installation
- Complies with NEC section 406.5 (E) for use in countertops or similar work surfaces

- Ingress Protection Rated



1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Countertop Box Kits

with Stainless Steel Boxes and Covers

NEW!
ROUND COVERS

with ROUND Stainless Steel Trapdoor Covers

Catalog Number	UPC/DEI/NAED Mfg. #018997	Description Countertop Box Kits	Installed UL LISTED Device	Unit/Std Pkg
FLBT4465USS	22942	Steel box with installed	20A decorator-style TR receptacle, with (2) USB ports	1
FLBT4465SS	22941	UL Listed device.	20A decorator-style TR receptacle	1
FLBT4465GSS	22940	ROUND Stainless steel trapdoor cover	Tamper and Weather Resistant (TWR) 20A decorator-style GFCI receptacle	1



FLBT4465USS



FLBT4465SS



FLBT4465GSS

with
20A decorator-style
TR receptacle
w (2) USB ports

with
20A decorator-style
TR receptacle

with
TWR 20A decorator-style
GFCI receptacle

TRY THESE KITS TOO!

with RECTANGULAR Stainless Steel or Black COVERS

Catalog Number	UPC/DEI/NAED Mfg. #018997	Description Countertop Box Kits	Installed UL LISTED Device	Unit/Std Pkg
FLBT4400USS	00752	Steel box with installed	20A decorator-style TR receptacle, with (2) USB ports	1
FLBT4400SS	00751	UL Listed device.	20A decorator-style TR receptacle	1
FLBT4400GSS	00753	Stainless steel trapdoor cover	Tamper and Weather Resistant (TWR) 20A decorator-style GFCI receptacle	1



FLBT4400USS



FLBT4400SS



FLBT4400GSS

Black Trapdoor Covers

Catalog Number	UPC/DEI/NAED Mfg. #018997	Description Countertop Box Kits	Installed UL LISTED Device	Unit/Std Pkg
FLBT4400UBL	00771	Steel box with installed	20A decorator-style TR receptacle, with (2) USB ports	1
FLBT4400BL	00768	UL Listed device.	20A decorator-style TR receptacle	1
FLBT4400GBL	00770	Black trapdoor cover	Tamper and Weather Resistant (TWR) 20A decorator-style GFCI receptacle	1



FLBT4400GBL



Arlington®

1 Stauffer Industrial Park
Scranton, PA 18517

800/233.4717

Fax 570/562.0646

www.aifittings.com

Distributed by

Patents pending FLBT4465 0317/25M