



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **FLED15R1AUNV8CSW 15W Led Flood 3K/4K/5K Select 2100LM WHT 120/277V** *Keystone Technologies*

Catalog Number	FLED15R1AUNV8CSW
Manufacturer	Keystone Technologies
Description	15W Led Flood Light Feat. Color Select, Rectangular Series 1 With Built In Photocell. 120-277V Input, 3000K/4000K/5000K. White Housing. Wide Beam Spread, Universal Mount (1/2IN Knuckle Mount With Yoke Mount Option Included) Dimmable
Weight per unit	0.3260 (lbs/each)
Product Category	Lighting

### **Features**

Ballast Type	N/A
beam angle	N/A
Circuit Type	N/A
Input Voltage	120-277V
ip rating	IP65
lumens	2100
Nominal Length	N/A
Nominal Size	Rectangular
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	Photocell only
Wattage	15
Wire Type	N/A

### **Material, Color, and Finish**

Base Type	N/A
color rendering index (cri)	>80 Deg
color temperature	N/A
housing color	White

### **Descriptions**

Construction	N/A
Description	KT-FLED15-R1A-UNV-8CSB-VDIM-W
extra long description	Key KT-FLED15-R1A-UNV-8CSB-VDIM-W 7
Long Description	15W LED Flood Light feat. Color Select, Rectangular Series 1 with built in photocell. 120-277V Input, 3000K/4000K/5000K. White Housing. Wide Beam Spread, Universal Mount (1/2in Knuckle Mount with Yoke Mount option included) Dimmable
Product Type	70W Equiv., 15W, 2100 Lumens Built In Photocell. Univl MT (1



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00843654128955
Manufacturers Part Number	KT-FLED15-R1A-UNV-8CSB-VDIM-W
UPC	843654128955

## Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
----------------------	---

## Packaging

Carton	1
Weight Per each	0.326

## Uses, Certifications, and Standards

Energy Star	N
-------------	---