



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FLM52 52W Led Flood 50K 4957LM 120-277V

Hubbell Lighting/Current Hli

Catalog Number	FLM52
Manufacturer	Hubbell Lighting/Current Hli
Description	N/A, Mounting Type: Knuckle (1/2 In X 14 NPS), Light Distribution: Nema 6X6 (HXV), Wattage: 52 W, 70 Cri, Light Output: 4957 LM, Voltage Rating: 120-277 Vac, Color: Dark Bronze, Epa Effective Projected Area: 0, 54 FT².
Weight per unit	8.5 (lbs/each)
Product Category	Led Floodlights

Features

Fixture Type	Floodlighting
Lamp Type	LED
lumens	4957
Voltage Rating	120-277 VAC

Material, Color, and Finish

Color	Dark Bronze
-------	-------------

Descriptions

Description	52W LED FLOOD 50K 4957LM 120-277V
extra long description	HUB-LT FLM-52 FLM Architectural LED
Long Description	N/A, Mounting Type: Knuckle (1/2 in x 14 NPS), Light Distribution: NEMA 6x6 (HxV), Wattage: 52 W, 70 CRI, Light Output: 4957 lm, Voltage Rating: 120-277 VAC, Color: Dark Bronze, EPA Effective Projected Area: 0,54 ft².
Product Type	FLM Architectural Led Flood

Manufacturer Information

Brand	Beacon_Products
GTIN	00785988033607
Manufacturers Part Number	FLM-52
UPC	785988033607

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Floodlighting

Packaging

Carton	1
Weight Per each	8.52



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Automotive

Dealers;Educational;Healthcare;Hospitality;Manufacturing;Offices;Retail;V

Mounting

Knuckle (1/2 in x 14 NPS)

standard

CSA;IP Rated;UL1598A;Wet Listed