



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10070 E. 40th Ave.
80238-0000, CO Denver
Phone: 720-259-9108
Fax: 720-259-9109



FMLWL24840 2' Led Wrap 40K 1200LM

Lithonia Lighting - Acuity

Catalog Number	FMLWL24840
Manufacturer	Lithonia Lighting - Acuity
Description	The Low-Profile 2-FT. Long FMLWL Led Wraparound By Lithonia Lighting® Provides Efficient and Economical Ambient Lighting In Surface-Mount Applications With Full Dimensions Of 24.5-In X 5.5-In X 2.6-In. It Is Ideal For Many Applications Including Corridors, Kitchens, Breakrooms, Utility Work Areas and Stairways.
Weight per unit	2.4 (lbs/each)
Product Category	Led Surface Architectural & SP

Features

average life	50,000
dimensions	24.5 x 5.5 x 2.6
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	1400 LM
Material	Steel
pallet quantity	224
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120 V
Warranty	5
Wattage	19.6

Material, Color, and Finish

Color	White
color rendering index (cri)	80-89
Finish	Gloss
Style	CONTEMPORARY

Dimensions and Weight

Height	2.58
Length	24.45
Width	5.48



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10070 E. 40th Ave.
80238-0000, CO Denver
Phone: 720-259-9108
Fax: 720-259-9109

Descriptions

Description	2' LED WRAP 40K 1200LM
extra long description	LITH FMLWL 24 840 Wraparound, 2FT x
Features	Contractor Select
Long Description	The low-profile 2-ft. long FMLWL LED Wraparound by Lithonia Lighting® provides efficient and economical ambient lighting in surface-mount applications with full dimensions of 24.5-in x 5.5-in x 2.6-in. It is ideal for many applications including corridors, kitchens, breakrooms, utility work areas and stairways.
Product Type	Wraparound

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00888791197921
Manufacturers Part Number	FMLWL 24 840
UPC	888791197921

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Wraparound

Trade Size

aperture size	2FT,4FT
---------------	---------

Packaging

Carton	1
Weight Per each	2.4

Uses, Certifications, and Standards

Application	Government,Hospitality,Offices & Banks,Residential,Utility, Closet
environmental conditions	Indoor
Mounting	SURFACE
standard	cUL,UL