



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FNO6 6A 500V TD CT Midget Fuse

*Bussmann Fuses*

Catalog Number	FNO6
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series FNO Fuse, Time-Delay, Motor Control Transformers, Circuits With In-Rush Currents, 6 A, Non-Indicating, Ferrule End X Ferrule End, 10 Kaic At 500 Vac, Nickel-Plated Bronze Endcap, Standard, 500 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

### Features

amperage rating	6 Amp
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
interrupt rating	10000 Amp (RMS Symmetrical)
Material	Nickel-plated bronze endcap
media	Yes
Voltage Rating	500 VAC

### Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

### Descriptions

Description	6A 500V TD CT MIDGET FUSE
extra long description	BUSS FNO-6 BUSS MIDGET FUSE
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series FNO fuse, Time-delay, Motor control transformers, Circuits with in-rush currents, 6 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 500 Vac, Nickel-plated bronze endcap, Standard, 500 V
Product Type	Buss Midget Fuse
Special Features	Nickel Plated Brass Endcap

### Manufacturer Information

Brand	Eaton
GTIN	00051712786065
Manufacturers Part Number	FNO-6
UPC	051712786065



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... MIDGET FUSES

Type ..... FUSE

## Packaging

Carton ..... 10

Weight Per each ..... 0.02

## Uses, Certifications, and Standards

Application ..... Ind Facilities & Factories - Facility: Safety and Security Systems

standard ..... RoHS Compliant,CE Marked