




# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FP14835ECO FP14835ECO Fluor Lamp

*Sylvania-Ledvance*

|                  |                                                                                                  |
|------------------|--------------------------------------------------------------------------------------------------|
| Catalog Number   | FP14835ECO                                                                                       |
| Manufacturer     | Sylvania-Ledvance                                                                                |
| Description      | 14W, T5 Pentron Fluorescent Lamp, 3500K Color Temperature, Rare Earth Phosphor, 85 Cri, Ecologic |
| Weight per unit  | 0.1300 (lbs/each)                                                                                |
| Product Category | Linear Fluorescent Straight La                                                                   |

### Features

|                           |                        |
|---------------------------|------------------------|
| amperage rating           | Ballast Dependent      |
| average life              | 20000                  |
| Base                      | Miniature Bipin        |
| bulb type                 | T5                     |
| lumens                    | 1,200                  |
| Shape                     | T5                     |
| start type                | Programmed Rapid Start |
| total harmonic distortion | Ballast Dependent      |
| Voltage                   | 230.00 V               |
| Voltage Rating            | Ballast Dependent      |
| Wattage                   | 14                     |

### Material, Color, and Finish

|                             |                 |
|-----------------------------|-----------------|
| color rendering index (cri) | 85              |
| color temperature           | 3500            |
| Finish                      | Phosphor Coated |

### Dimensions and Weight

|          |       |
|----------|-------|
| Diameter | 0.625 |
|----------|-------|

### Descriptions

|                        |                                                                                                  |
|------------------------|--------------------------------------------------------------------------------------------------|
| Description            | FP14835ECO FLUOR LAMP                                                                            |
| extra long description | SYL FP14/835/ECO/20908 FP14835ECO 4                                                              |
| Long Description       | 14W, T5 PENTRON fluorescent lamp, 3500K color temperature, rare earth phosphor, 85 CRI, ECOLOGIC |
| Product Type           | FP14835ECO 40/CS 1/Sku                                                                           |

### Manufacturer Information

|                           |                    |
|---------------------------|--------------------|
| Brand                     | SYLVANIA           |
| GTIN                      | 00046135209086     |
| Manufacturers Part Number | FP14/835/ECO/20908 |
| UPC                       | 046135209086       |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fluorescent

Type ..... FLUORESCENT

## Packaging

Carton ..... 1

Package ..... 40

Weight Per each ..... 0.13

## Uses, Certifications, and Standards

Application ..... Commercial/Residential