



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FS2 Single Gang Cast Iron Box W/ 3/4" Opening

Crouse-Hinds

Catalog Number	FS2
Manufacturer	Crouse-Hinds
Description	Device Box, Single Gang Box Style, Electrogalvanized and Aluminum Acrylic Paint, Silver, Shallow, 3/4 In Trade Size, 1 Hub, 3/4 In Hub Size, 2.75 In Width, 6.03 In Height, Surface Mount, 2.17 LB/Ea
Weight per unit	2.2 (lbs/each)
Product Category	FS & FD Type Boxes & Covers

Features

Cable Entry	(1) End
dimensions	5.1600 IN X 1.8800 IN X 2.7500 IN
Material	Electrogalvanized With Aluminum Acrylic Painted Feraloy Iron Alloy

Dimensions and Weight

Size	3/4 in
------	--------

Descriptions

Description	SINGLE GANG CAST IRON BOX W/ 3/4" OPENING
extra long description	CRS-H FS2 3/4 NPT CST IRON FS BX SG
Features	Crouse-Hinds series FS and FD device boxes are installed in non-hazardous area conduit systems to accommodate wiring devices, act as pull boxes or provide openings for taps and splices. They are suitable for use in wet locations when used with gasketed covers. FS and FD device boxes are available in two box depths with a wide variety of gang configurations, hub configurations and hub sizes. They are manufactured in cast iron, aluminum, stainless steel and malleable iron. Malleable iron boxes are also a
Special Features	Configuration Type FS, With Mounting Lug and Ground Screw, Dimension 2-3/4 In Width X 1-7/8 In Depth X 5-5/32 In Height

Manufacturer Information

Brand	Eaton
GTIN	00782274405902
UPC	782274405902

Taxonomies, Classifications, and Categories

Category Description	FS BOXES AND COVERS
Type	DEVICE BOX



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	2.17

Uses, Certifications, and Standards

Mounting	FLUSH
standard	UL 514, CSA C22.2, Federal Specification W-C-5860