



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FSS375 3G 3/4 Mall FSS Box *Appleton/Oz Gedney*

Catalog Number	FSS375
Manufacturer	Appleton/Oz Gedney
Description	Unilets FSS Shallow Depth 3-Gang Cast Device Box, Number Of Outlet: 2, Material: Malleable Iron, Size: 3/4 In, Cable Entry: (2) 3/4 In Hub, Cubic Capacity: 40 Cu-In, Knockouts: No, Height: 4.56 In, Width: 6.44 In, Depth: 2 In, Finish: Triple-Coat (Zinc Electroplate, Chromate and Epoxy Powder Coat), Standard: UI 514 A, UI File Number E2527, Csa C22.2 No. 18.1, Csa 001472 Certified, Nema FB-1, For Use With Threaded Metal Conduit and Imc
Weight per unit	3.5 (lbs/each)
Product Category	FS & FD Type Boxes & Covers

Features

Cable Entry	(2) 3/4 IN Hub
Knockouts	FALSE
Material	Malleable Iron
number of outlet	2

Dimensions and Weight

Size	3/4
------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	3G 3/4 MALL FSS BOX
extra long description	APP FSS-3-75 UNILET 3/4 THRD 3 GANG
Long Description	UNILETS FSS Shallow Depth 3-Gang Cast Device Box, Number Of Outlet: 2, Material: Malleable Iron, Size: 3/4 IN, Cable Entry: (2) 3/4 IN Hub, Cubic Capacity: 40 CU-IN, Knockouts: No, Height: 4.56 IN, Width: 6.44 IN, Depth: 2 IN, Finish: Triple-Coat (Zinc Electroplate, Chromate And Epoxy Powder Coat), Standard: UL 514 A, UL File Number E2527, CSA C22.2 No. 18.1, CSA 001472 Certified, NEMA FB-1, For Use With Threaded Metal Conduit And IMC
Product Type	Unilet 3/4 THRD 3 Gang
Special Features	Accommodate wiring devices such as switches and receptacles;Accurately tapped, tapered threads for tight, rigid joints, ground continuity;Both malleable iron and aluminum boxes have ridge top construction for positive cover/gasket/box fit;Corrosion-resistant ideal for indoor and outdoor installations;Internal grounding screws standard;Malleable iron for high tensile strength and ductility provides greater resistance to impact and shock;Permit access to conductors for maintenance;Provide excellent service i

Manufacturer Information

Brand	Appleton
GTIN	00781381353106
Manufacturers Part Number	FSS-3-75
UPC	781381353106

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FSS Shallow Depth 3-Gang Cast Device Box

Packaging

Carton	1
Package	10
Weight Per each	3.48

Uses, Certifications, and Standards

Application	For Use With Threaded Metal Conduit And IMC
standard	UL 514 A, UL File Number E2527, CSA C22.2 No. 18.1, CSA 001472 Certified, NEMA FB-1