



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FSC27 2G SW Box Feed-Thru *Crouse-Hinds*

Catalog Number	FSC27
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet FS Device Box, Shallow, Feraloy Iron Alloy, Two-Gang, Tandem, C Shape, 3/4"
Weight per unit	4.7 (lbs/each)
Product Category	FS & FD Type Boxes & Covers

Features

Cable Entry	(1) Each Side
dimensions	10.8100 IN X 1.8800 IN X 2.7500 IN
Material	Natural Finished Sand Copper-Free Aluminum

Dimensions and Weight

Size	3/4 in
------	--------

Descriptions

Description	2G SW BOX FEED-THRU
extra long description	CRS-H FSC27 3/4 NPT CST IRN BX TWO
Features	Crouse-Hinds series FS and FD device boxes are installed in non-hazardous area conduit systems to accommodate wiring devices, act as pull boxes or provide openings for taps and splices. They are suitable for use in wet locations when used with gasketed covers. FS and FD device boxes are available in two box depths with a wide variety of gang configurations, hub configurations and hub sizes. They are manufactured in cast iron, aluminum, stainless steel and malleable iron. Malleable iron boxes are also a
Long Description	Eaton Crouse-Hinds series Condulet FS device box, Shallow, Feraloy iron alloy, Two-gang, tandem, C shape, 3/4"
Product Type	3/4 NPT CST Irn BX Two GNG MTG Lugs TNDM
Special Features	Configuration Type FSC, With Mounting Lug and Ground Screw, Dimension 2-3/4 In Width X 1-7/8 In Depth X 6-1/32 In Height

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274411408
Manufacturers Part Number	FSC27
UPC	782274411408

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	DEVICE BOX



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	4.65

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Mounting	SURFACE
standard	UL 514, ANSI C33.84, CSA C22.2, Federal Specification W-C-5860