



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1336 Swisco Road  
70665-0000, LA Sulphur  
Phone: 337-533-8019  
Fax: 337-533-8055



## GBC210 10CKT Isol Ground Bar

*Nsi Industries*

Catalog Number	GBC210
Manufacturer	Nsi Industries
Description	The Nsi GBC2-10 Copper Isolated Ground Bar Mounts Onto Most Surfaces Using The High-Strength Glass-Filler Polyester Base, Then Fits Up to 10 Copper Cables In The 2 to 14 Awg Size Range. The High-Conductivity Copper Body Is Rated For Use With Copper Wiring and Forms Reliable Connections Using The Simple Tightening Screw Lug Design. Stock Products You Can Rely Onâ€”Stock Nsi.
Weight per unit	1.4 (lbs/each)
Product Category	Ground Rods & Grounding System

### Features

Conductor Size	2-14 AWG
insulation	Glass Filled Polyester Base
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Conductor Material	Copper
--------------------	--------

### Dimensions and Weight

Length	4.07
Size	2-14 AWG



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1336 Swisco Road  
70665-0000, LA Sulphur  
Phone: 337-533-8019  
Fax: 337-533-8055

## Descriptions

Description	10CKT ISOL GROUND BAR
extra long description	NSI GBC2-10 Copper Isolated Ground
Features	NSI grounding and bonding products rise to the occasion in a wide variety of professional environments with excellent material quality and flexible designs. These copper isolated grounding bars offer a convenient and reliable solution for grounding multiple copper cables. The high-conductivity copper bar and high-strength glass-filled polyester base are both designed for long-lasting performance in a variety of environments. Designed to fit a range of different wire sizes by using a screw lug design, these
Long Description	The NSI GBC2-10 Copper Isolated Ground Bar mounts onto most surfaces using the high-strength glass-filler polyester base, then fits up to 10 copper cables in the 2 to 14 AWG size range. The high-conductivity copper body is rated for use with copper wiring and forms reliable connections using the simple tightening screw lug design. Stock products you can rely onâ€”stock NSI.
Product Type	Copper Isolated Ground Bar, 2-14 Awg Wire Range, 10 Circuit
Special Features	Copper Bar With Isolation Base - 10 Circuits

## Manufacturer Information

Brand	Polaris
GTIN	00662381010735
Manufacturers Part Number	GBC2-10
UPC	662381010735

## Taxonomies, Classifications, and Categories

Category Description	EXOTHERMIC GROUNDING PRODUCTS
Type	Isolated Ground Bars

## Packaging

Carton	1
Package	3
Weight Per each	1.4

## Uses, Certifications, and Standards

Application	Grounding Wire
-------------	----------------